



#### NOTES:

1. INSTALLATION TO BE CARRIED OUT IN COMPLIANCE WITH THE SPECIFICATIONS AND INSTRUCTIONS PROVIDED BY THE MANUFACTURER.
2. A TRENCH MUST BE DUG WITH A WIDTH THAT EXCEEDS THE U-DRAIN'S OVERALL WIDTH BY AT LEAST 12" (6" MINIMUM ON EACH SIDE) AND A DEPTH THAT SURPASSES THE OVERALL DEPTH OF THE U-DRAIN BY AT LEAST 6".

FINISH SPECIFICATIONS  
HOT DIP GALVANIZED

UNLESS OTHERWISE SPECIFIED: TOLERANCE:  X ± 0.1 XX ± 0.01 XXX ± 0.005 ANGLE ± 0.5  DO NOT SCALE PRINT	THIS DRAWING CONFORMS TO ASME 14.5M - 1994 FOR DOCUMENTATION PRACTICES		 <small>NOTICE TO PERSONS RECEIVING THIS DRAWING: NORSTAR INDUSTRIES CLAIMS PROPRIETARY RIGHTS TO THE MATERIAL SHOWN ON THIS DRAWING. THE DRAWING MAY NOT BE REPRODUCED FOR ANY REASON WITHOUT WRITTEN PERMISSION FROM NORSTAR INDUSTRIES</small>	PRODUCT SERIES		STANDARD DRAWING - IN AUTODESK INVENTOR 3D MODEL	
	THIRD ANGLE PROJECTION 			NAME		DATE	
				DRAWN BY JC Dallarte		23/03/2023	
MATERIAL				DESIGNER Randy Martens		04/11/2008	
				CHECKER			
				PART NO. <b>1 1 7 2 4</b>		REV	
SHEET SIZE A MASSI N/A							
THICKNESS			SCALE SEE ABOVE		SHEET NO. 1 OF 1		

NOTICE TO PERSONS RECEIVING THIS DRAWING: NORSTAR INDUSTRIES CLAIMS PROPRIETARY RIGHTS TO THE MATERIAL SHOWN ON THIS DRAWING. THE DRAWING MAY NOT BE REPRODUCED FOR ANY REASON WITHOUT WRITTEN PERMISSION FROM NORSTAR INDUSTRIES