




FASTEN MEMBRANE AND FLASH CURB OR WALL WITH CURED EPDM MEMBRANE FOLLOWING STANDARD PROCEDURES USING BONDING ADHESIVE and QA SEAM TAPE.




CUT A 9"x9" (23cm x 23cm) SECTION OF QUICK-APPLIED UNCURED EPDM FLASHING AND MAKE ROUNDED CORNERS AS SHOWN.



AFTER APPLYING EPDM PRIMER, REMOVE AND REPLACE POLY BACKING. FOLD FLASHING IN HALF WITH ROUNDED PORTION TURNED UP. CENTER FLASHING ON CORNER AND FIRMLY PRESS AGAINST VERTICAL SURFACE.



ROLL AND CREASE FLASHING TIGHTLY INTO ANGLE CHANGE AND FIRMLY ROLL FLASHING ONTO THE DECK MEMBRANE.



AFTER ADHERING, ROLL WITH A TWO INCH WIDE STEEL HAND ROLLER. PAY PARTICULAR ATTENTION TO THE STEP OFFS AND ANGLE CHANGES.

DIMENSIONS		cm	
(A)	6"	15	TO
	9"	23	


NOTES:

- FOR PROJECTS WITH 25 & 30-YEAR WARRANTIES OR WHEN USING 90-MIL MEMBRANE, REFER TO DETAIL VGC-15.7A FOR REQUIRED FLASHING ENHANCEMENTS.
- A HEAT GUN MUST BE USED WHEN FORMING QUICK-APPLIED UNCURED EPDM FLASHING IN COLDER TEMPERATURES.

MAXIMUM WARRANTY: 20 YEARS



OUTSIDE CORNER WITH QUICK-APPLIED UNCURED EPDM FLASHING (1 PIECE)



THERMOSET ROOFING SYSTEM
VGC-15.7