




DESIGN 1



DESIGN 2



DESIGN 3



DESIGN 4

DESIGN GUIDELINES — BASE DEPTH

LOAD DESCRIPTION	CBR 2 - 4%	CBR > 4%
Heavy Fire Truck Access & H/HS25 loading. Typical 110 psi (758 kPa) tire pressure. Single axle loadings of 40 kips (178 kN). Gross vehicle weight of 90,000 lbs (40.1 MT).	Design 1 - 6" Base	Design 2 - 4" Base
Heavy Fire Truck Access & H/HS20 loading. Typical 110 psi (758 kPa) tire pressure. Single axle loadings of 32 kips (145 kN). Gross vehicle weight of 80,000 lbs (36.3 MT).	Design 1 - 6" Base	Design 2 - 4" Base
Light Fire Truck Access & H/HS15 loading. Typical 85 psi (586 kPa) tire pressure. Single axle loadings of 24 kips (110 kN). Gross vehicle loads of 60,000 lbs (27.2 MT).	Design 2 - 4" Base	Design 3 - 2" Base
Utility & Delivery Truck Access & H/HS10 loading. Typical 60 psi (414 kPa) tire pressure. Single axle loadings of 16 kips (75 kN). Gross vehicle loads of 40,000 lbs (18.1 MT).	Design 3 - 2" Base	Design 3 - 2" Base
Cars & Pick-up Truck Access. Typical 45 psi (310 kPa) tire pressure. Single axle loadings of 4 kips (18 kN). Gross vehicle loads of 8,000 lbs (3.6 MT).	Design 4 - No Base	Design 4 - No Base
Trail Use. Loading for pedestrian, wheelchair, equestrian, bicycle, motorcycle and ATV traffic.	Design 4 - No Base	Design 4 - No Base

Notes:

1. This information is based on the use of Geoblock 5150 manufactured by Reynolds Presto Products, Inc. All rights reserved. Any use of this information for any rigid porous paver product other than that manufactured by Reynolds Presto Products, Inc. is strictly prohibited and makes this information invalid.
2. Engineered base is a homogenous mixture consisting of open graded crushed aggregate having an AASHTO # 5 or similar designation blended with pulverized topsoil and a void component generally containing air and/or water. This homogenous mixture will promote vegetative growth and provide required structural support. The aggregate portion shall have a particle range from 9.5 mm to 25 mm (0.375 to 1.0 in) with a D50 of 13 mm (0.5 in). The percentage void-space of the aggregate portion when compacted shall be at least 30%. The pulverized topsoil portion shall equal 33% +/- of the total volume and be added and blended to produce a homogenous mixture prior to placement.
3. If required, provide a non-woven geotextile separation layer and install in accordance with Manufacturer recommendations including overlaps based on sub grade CBR.
4. Connect Geoblock 5150 panels with the interlocking offset tab so that adjacent sections have horizontally level profiles.
5. Refer to the Geoblock 5150 Design and Construction Overview for a complete description of the design and construction methods.

REYNOLDS PRESTO®
PRODUCTS, INC.
670 NORTH PERKINS STREET
APPLETON, WI 54914
920-738-1342
WWW.PRESTOCEO.COM

GEOBLOCK 5150
POROUS PAVEMENT SYSTEM

PRESTO®, GEOSYSTEMS®, AND GEOBLOCK® ARE REGISTERED TRADEMARKS OF REYNOLDS PRESTO PRODUCTS, INC.

DATE:	MARCH 2020	FILE NAME	GB5150B1.dwg
SCALE:	NTS	SHEET	1