



NOTES:

1. REMOVE ALL LEAD AND OTHER FLASHING BEFORE INSTALLING QUICK-APPLIED PIPE SEAL.
2. TEMPERATURE OF PIPE PENETRATION MUST NOT EXCEED 180°F (82°C).
3. PRE-MOLDED PIPE FLASHING MUST HAVE RIB INTACT AT THE TOP EDGE REGARDLESS OF PIPE DIAMETER.
4. DECK FLANGES OF THE QUICK-APPLIED PIPE SEAL SHALL NOT BE OVERLAPPED, CUT OR APPLIED OVER ANY ANGLE CHANGE.
5. USE DETAIL VGC-8.1A WHEN PIPE BOOT INTERSECTS A SPLICE ON 25/30 YEAR WARRANTIES.
6. ON MECHANICALLY-FASTENED ROOFING SYSTEMS, REFER TO DETAIL VGMA-8.1.

DIMENSIONS		cm	
(A)	1/2"	1.5	TO
	6"	15	
(B)	3"	7.5	



MAXIMUM WARRANTY: 30 YEARS

QUICK-APPLIED
PIPE SEALTHERMOSET
ROOFING SYSTEM

VGC-8.1