



* 19" X 36"
SERVICE OPENING



ELECTRICAL REQUIREMENTS

USA (DOMESTIC) : 115 vac - 60 Htz WITH A 15 amp BRANCH CIRCUIT
INTERNATIONAL : 220/240 vac - 50/60 Htz WITH A MAX. 8 amp BRANCH CIRCUIT

275 - 43-1/2" H
GLAZING ROUGH OPENING =
47-3/4" W (1213 mm) x 43-3/4" H (1111 mm)
MASONRY ROUGH OPENING =
48" W (1219 mm) x 44" H (1118 mm)

47-1/2" W X 35-3/4" H
GLAZING ROUGH OPENING =
47-3/4" W (1213 mm) x 36" H (914 mm)
MASONRY ROUGH OPENING =
48" W (1219 mm) x 36-1/4" H (921 mm)

UNIT SPECIFICATIONS:

104/120 VOLTS
3 ACTUAL UNIT AMPS
60 HZ

* TWO STANDARD WINDOW HEIGHTS

43-1/2" H WITH 19" W x 36" H SERVICE OPENING
35-3/4" H WITH 19" W x 28" H SERVICE OPENING

275-E