

1

FASTEN MEMBRANE AND FLASH CURB OR WALL WITH CURED EPDM MEMBRANE FOLLOWING STANDARD PROCEDURES USING BONDING ADHESIVE AND QA SEAM TAPE AT MEMBRANE SPLICE.

2

CENTER FOLD LINE
QUICK APPLIED UNCURED FLASHING

CUT A 4-1/2"x6" AND 9"x12" SECTION OF QUICK APPLIED UNCURED EPDM FLASHING AND ROUND CORNERS AS SHOWN.

3

CLEAN THE DRY SPLICE AREA OF THE EPDM WITH EPDM PRIMER; APPLY LAP SEALANT 2" (51mm) MIN. FROM THE CURB AS SHOWN

4

POLY FILM

AFTER APPLYING LAP SEALANT, REMOVE & REPLACE POLY BACKING ON FLASHING. FOLD 6"x6" FLASHING IN HALF WITH ROUNDED PORTION TURNED UP. CENTER ON CORNER & FIRMLY PRESS AGAINST VERTICAL SURFACE

5

ROLL & CREASE FLASHING TIGHTLY INTO ANGLE CHANGE & FIRMLY ROLL FLASHING ONTO THE DECK MEMBRANE

6

AFTER ADHERING, ROLL WITH A TWO INCH WIDE STEEL HAND ROLLER. PAY PARTICULAR ATTENTION TO THE STEP OFFS AND ANGLE CHANGES

7

CLEAN THE SPLICE AREA WITH EPDM PRIMER. INSTALL THE 9"x12" SECTION OF QUICK APPLIED UNCURED EPDM FLASHING TO EXTEND A MINIMUM 2" BEYOND THE PREVIOUSLY APPLIED 4-1/2"x6" FLASHING (STEPS 4-6).

8

OVERLAY THE CORNER WITH 2 PIECES OF 9"x12" QUICK APPLIED UNCURED EPDM FLASHING AS SHOWN

9

SEAL ALL EDGES WITH LAP SEALANT AS SHOWN



OUTSIDE CORNER FLASHING FOR PROJECTS WITH 90-MIL MEMBRANE OR 25 & 30 YEAR WARRANTIES

→ EPDM MEMBRANE
→ APPROVED SUBSTRATE
→ SEE NOTE(S)

0

THERMOSET ROOFING SYSTEM
VGC-15.8