



PRE-MOLDED INSIDE CORNER BEFORE INSTALLATION

NOTES:

1. POSITION FASTENING PLATES 6" TO 9" (152 TO 229mm) FROM THE CORNER AND 1/2" TO 1" (13 TO 25mm) FROM EDGE OF MEMBRANE.
2. APPROXIMATELY 1/8" (3mm) DIAMETER BEAD OF CUT-EDGE SEALANT IS REQUIRED ON CUT EDGES OF REINFORCED TPO MEMBRANE AND RECOMMENDED ON CUT EDGES OF VERSIFLEX PVC MEMBRANE.
3. REFER TO VERSICO SPECIFICATIONS FOR ACCEPTABLE VERSICO FASTENERS AND PLATES.
4. WHEN USING 60 OR 80-MIL MEMBRANE, APPLY A 4-1/2" (114mm) DIAMETER "T-JOINT" COVER AT ALL FIELD SPLICE INTERSECTIONS.

DIMENSIONS	mm		
<b>A</b>	6"	152	APPROX.
<b>B</b>	6"-9"	152-229	
<b>C</b>	45-DEGREES APPROX.		



**PRE-MOLDED INSIDE CORNER FLASHING**

THERMOPLASTIC ROOFING SYSTEM

**TPC-15.1**