

TRUSS TO WALL
CONNECTION
BY ROOF TRUSS MFG.

TRUSS BOTTOM CHORD,
(N.I.C.)

TOP TRACK

3/4" MAX.

LOAD BEARING WALL STUDS

BEARING TOLERANCE

ROOF TRUSS
@ 48" O.C. (N.I.C.)

NOTE:
SPLICE TOP TRACK AT
DOUBLE STUD LOCATIONS
ONLY.

CONTINUOUS TOP
TRACK.

1/8" 1-12

(1) #10-16 SCREW
@ EACH FLANGE

STEEL STUDS BETWEEN
ROOF TRUSSES.


ALTERNATE DOUBLE
STUD ATTACHMENT

CONNECTION BY
ROOF TRUSS MFG.
ATTACH DIRECTLY
TO WALL STUD

(2) #10-16 SCREWS
@ 12" O.C.

DOUBLE STUDS TO ALIGN
BELOW EA. ROOF TRUSS

TELLING™



BUILDSTRONG

6272 CENTER STREET
MENTOR, OHIO 44060
PHONE: 440-974-3370

DETAIL IS FOR
REFERENCE ONLY.
NOT FOR CONSTRUCTION.

DETAIL PROVIDED BY:



100 CAMELOT DRIVE
FOND DU LAC, WI 54935
PHONE: (920) 926-9800

TRUSS BEARING DETAIL