

TOI	R	M	A	®	
AUTOMATIC					


TX9200SL AC AUTOMATIC SLIDING DOOR SYSTEM

BIPART SURFACE MOUNT OUTSIDE SLIDE "P" PANEL APPLICATION (P-SX-SX-P) W/ELECTRIC LOCK & FLUSH MOUNT EXIT PANIC HW


JOB NAME: _____ DATE:___

DOOR LOCATION: ______ DOOR NO: _____SHEET ___OF_






4 1/2"



PLAN



2 HORIZONTAL SECTION

*SEE APPENDIX FOR THRESHOLD OPTIONS & SURFACE MOUNT CONCEALED VERTICAL ROD EXIT PANIC HARDWARE OPTION

N	Ο.	TI	F	c	•

- 1. DETAILS NOT TO SCALE
- 2. ELECTRICAL REQUIREMENTS:
 120 VAC, 5 AMPS MIN. TO OPERATOR BY
 ELECTRICAL CONTRACTOR
- 3. DOOR PACKAGES ARE INDIVIDUALLY ENGINEERED TO FIT YOUR JOB REQUIREMENTS

SAMPLE PACKAGE WIDTH INFORMATION						
PACKAGE WIDTH [UW] (*)	CLEAR DOOR OPENING [CDO] (*)	PANEL WIDTH [PW] (*)	EMERGENCY BREAKOUT WIDTH (*)			
2*[CDO] + 23 1/8	[UW] ₂ - 11 9/ ₁₆ -OR- 2*[PW] - 12 3/ ₈	[UW] ₄ + 7/ ₁₆	[UW] - 2*[PW] - 3 ½			
10'-0" [3048]	48 7/16" [1230]	30 7/16" [773]	55 11/16" [1414]			
12'-0" [3658]	60 7/16" [1535]	36 7/16" [926]	67 11/16" [1719]			
14'-0" [4267]	72 7/16" [1840]	42 7/16" [1078]	79 11/16" [2024]			
(*) CALCULATIONS BASED ON EQUAL PANELS, 2 1/8" NARROW STILES, & 1/4" GLASS						