



2

1



SCALE 1:10



B

B

A

A

NOTES:
 *ALL FORMING RADI ARE .125 UON

1. TOLERANCES:

- a. ANGLES: +/- 2°
- b. RADI: +/- /02
- c. CAMBER: +/- 1/8" IN 10'
- d. SKI: +/- 1/8" IN 10'
- e. DIVE: +/- 1/8" IN 10'
- f. FLARE: +/- 1/32" IN 10' OF ENDS OF PART

C, D & E ARE NON LINEAR DIMENSIONS

2. TOLERANCES ARE MEASURED IN 10' LENGHTS WITH PARY LAYING FLAT ON IT'S BACK.

UNLESS OTHERWISE SPECIFIED,
 DIMENSIONS ARE IN INCHES

.XX = ±.0-
 .XXX = ±.00-
 .XXXX = ±.000-

ANGULAR = ± °
 FRACTIONAL = ±

SURFACE FINISH

DO NOT SCALE DRAWING

BREAK ALL SHARP EDGES AND REMOVE BURRS

THIRD ANGLE PROJECTION



	NAME	DATE
DRAWN	MASON BURCHETTE	06/22/2026
CHECKED		
APPROVED		



TRUE METAL SUPPLY

TITLE		
TUFF-RIB		
019		
SIZE	DWG NO.	REV.
A	MRS-TR	
SCALE	WEIGHT	SHEET
1:5		1 of 1

MATERIAL
 80 KSI STEEL

FINISH
 SMP, PVDF, AZ55,
 TRU-STEEL HD

2

1