



NOTES:

1. INSTALLATION TO BE CARRIED OUT IN COMPLIANCE WITH THE SPECIFICATIONS AND INSTRUCTIONS PROVIDED BY THE MANUFACTURER.
2. A TRENCH MUST BE DUG WITH A WIDTH THAT EXCEEDS THE U-DRAIN'S OVERALL WIDTH BY AT LEAST 12" (6" MINIMUM ON EACH SIDE) AND A DEPTH THAT SURPASSES THE OVERALL DEPTH OF THE U-DRAIN BY AT LEAST 6".

FINISH SPECIFICATIONS
HOT DIP GALVANIZED

UNLESS OTHERWISE SPECIFIED: TOLERANCE: X ± 0.1 XX ± 0.01 XXX ± 0.005 ANGLE ± 0.5 DO NOT SCALE PRINT	THIS DRAWING CONFORMS TO ASME 14.5M - 1994 FOR DOCUMENTATION PRACTICES	 <small>NOTICE TO PERSONS RECEIVING THIS DRAWING: NORSTAR INDUSTRIES CLAIMS PROPRIETARY RIGHTS TO THE MATERIAL SHOWN ON THIS DRAWING. THE DRAWING MAY NOT BE REPRODUCED FOR ANY REASON WITHOUT WRITTEN PERMISSION FROM NORSTAR INDUSTRIES</small>	PRODUCT SERIES		STANDARD DRAWING - IN	
	THIRD ANGLE PROJECTION 		AUTODESK INVENTOR 3D MODEL			
			NAME		DATE	
MATERIAL		DESCRIPTION K to K 3' U-Drain	DRAWN BY	JC Dallarte	23/03/2023	
SHEET SIZE A MASS N/A			DESIGNER	Randy Martens	04/11/2008	
THICKNESS			CHECKER			
			PART NO.	11734		REV
		SCALE SEE ABOVE	SHEET NO. 1 OF 1			