








NOTES:

1. INSTALLATION TO BE CARRIED OUT IN COMPLIANCE WITH THE SPECIFICATIONS AND INSTRUCTIONS PROVIDED BY THE MANUFACTURER.
2. A TRENCH MUST BE DUG WITH A WIDTH THAT EXCEEDS THE SUMP'S OVERALL WIDTH BY AT LEAST 12" (6" MINIMUM ON EACH SIDE) AND A DEPTH THAT SURPASSES THE OVERALL DEPTH OF THE SUMP BY AT LEAST 6".

FINISH SPECIFICATIONS  
HOT DIP GALVANIZED



UNLESS OTHERWISE SPECIFIED: TOLERANCE:  X ± 0.1 XX ± 0.01 XXX ± 0.005 ANGLE ± 0.5  DO NOT SCALE PRINT	THIS DRAWING CONFORMS TO ASME 14.5M - 1994 FOR DOCUMENTATION PRACTICES		 <small>NOTICE TO PERSONS RECEIVING THIS DRAWING: NORSTAR INDUSTRIES CLAIMS PROPRIETARY RIGHTS TO THE MATERIAL SHOWN ON THIS DRAWING. THE DRAWING MAY NOT BE REPRODUCED FOR ANY REASON WITHOUT WRITTEN PERMISSION FROM NORSTAR INDUSTRIES</small>	PRODUCT SERIES		STANDARD DRAWING - IN AUTODESK INVENTOR 3D MODEL		
	THIRD ANGLE PROJECTION 			NAME		DATE		
				DRAWN BY		JC Dallarte	12/04/2023	
				DESIGNER		Randy Martens	29/05/2009	
MATERIAL			DESCRIPTION Sump Weldment 18 x 18 x 24 OSR Exit Hole Right	CHECKER		PART NO.		REV
SHEET SIZE A				MASS		N/A		11827
THICKNESS				SCALE		SEE ABOVE		SHEET NO. 1 OF 1