

DW-5015

RECESSED ACCESS DOOR

Application

• For installation in drywall surfaces when it is required to conceal the door panel

Product Features

- Recessed 5/8" to receive drywall
- Door flange is a textured galvanized steel taping bead with pre-punched holes

DW-5015 Access Door Specifications:

Material: Steel Door 22 gauge, Mounting Frame: 22 gauge

Door: Recessed 5/8"

Door Frame: Galvanized steel drywall taping bead on all sides

Hinge: Concealed.

Standard Latch: Slotted Screwdriver Cam Latch

Optional Latches/Locks: Cylinder lock and key, allen head cam latch, spanner head cam latch, torx head with security pin

Finish: Satin coat steel



DW-5015 STANDARD SIZES (other sizes available upon request)

Nominal Door Size W&H		Latches	Weight per Door	
Inches	mm		lbs.	kg.
12 X 12	305 x 305	1	5.20	2.4
16 X 16	406 x 406	1	5.90	2.7
18 X 18	457 X 457	1	8.10	3.7
24 X 24	610 X 610	1	14.50	6.6
24 X 36	610 X 914	2	20.20	9.2

Wall or ceiling opening is W + 3/8'' (9 mm) For detailed specifications see submittal sheet

