


NOTES:

1. REMOVE ALL LEAD AND OTHER FLASHING BEFORE INSTALLING FIELD-FABRICATED FLASHING.
2. TEMPERATURE OF PIPE PENETRATION MUST NOT EXCEED 180°F (82°C).
3. ACCEPTABLE WITH SQUARE OR RECTANGULAR STRUCTURAL TUBING WITH ROUNDED CORNERS UP TO 12" (30cm). USE DETAIL VGC-5 IF GREATER THAN 12" (30cm).
4. IN COLDER TEMPERATURES, A HEAT GUN MUST BE USED WHEN FORMING QUICK-APPLIED UNCURED EPDM OR CURED FLASHING.
5. ON MECHANICALLY FASTENED ROOFING SYSTEMS. REFER TO DETAIL VGMA-8.2.
6. MEMBRANE SECUREMENT IS REQUIRED AROUND ALL ROUND PIPE PENETRATIONS GREATER THAN 18" (46cm) IN DIAMETER.

| DIMENSIONS | | cm | |
|------------|------|-----|------|
| (A) | 1/2" | 1.5 | MIN. |
| (B) | 1" | 2.5 | MIN. |
| (C) | 3" | 7.5 | MIN. |

MAXIMUM WARRANTY: 20 YEARS

FIELD FABRICATED
PIPE WRAPTHERMOSET
ROOFING SYSTEM

VGC-8.2