

# AGSLPGTFT Datasheet

Liquid Petroleum **Gas Detector** 

0





Plug & Play Installation

In-Built Audible Alarm

### **Product Overview**

The TFT range of AGS detectors work in combination with the AGS Merlin range of Gas Detection panels and Utility Controllers. The AGSLPGTFT features a semiconductor sensor for industrial and commercial indoor applications. Compact, modern, digital design makes the units aesthetically pleasing and easy to install.

### **Popular Applications**



## **Technical Specification**

General							
Model:		Merlin Gas Detector TFT					
Target Gases:		LPG					
Size: (H x W x D)		5.51 x 3.74 x 1.18" (140 x 95 x 30mm)					
Housing Material:		ABS Polylac - PA765					
Mounting:		Safe Zone - Indoor use - Wall Mounted					
Weight:		Max. 1.77oz (0.05kg)					
User Interface							
Display:		1.8" TFT					
Screen Brightness:		Non-Adjustable					
Visual Indicators:		TFT visual. Green: Normal; Yellow: Pre-Alarm; Red: Alarm					
Audible Alarm:		>70dB @ 3.28ft (1m). Quiet conditions.					
Buttons:		None					
Language:	English						
Power Supply							
Power Consumption:		90mA Max @ 24vdc					
DC Power:		12-32 VDC - Nominal 24 VDC					
Internal Fuse:		None					
Equipment		1					
Overvoltage Category:		II					
Pollution Degree:		3					
I/O							
Relay:		Volt Free (Normally Closed / Common / Normally Open)					
		1x 30vdc 2A (Non-Latching)					
Environmental							
Ingress Protection:		Not Formally Evaluated					
Operating:		-10 ~ 50°C / 14 ~ 122°F 30 ~ 80% RH (non-condensing)					
Storage:		-25 ~ 50°C / -13~122F° up to 95% RH (non-condensing)					
Altitude Rating:		2000m					
Wiring							
Typical		#15AWG Power Pair; #18AWG Data Pair-Tinned copper.					
Approvals							
Electromagnetic Compatibility and		BS/IEC/EN 61010-1					
Electrical Safety		EMC EN 50270					
Other							
Communication		RS485 MODBUS RTU					
Gas Sensor	Indicating Range	Steps	Response (t90)	Recovery (t10)	Alarm: 1 (Pre alarm warning)	Alarm: 2	*EOL (Years)
Propane (LPG)	0-20%LEL	0.1	<30s	<30s	▼8% LEL	▼10% LEL	10



#### Area of coverage

Consider the coverage required and function of the area. Emphasis should be placed on airflow patterns and correct placement, not perceived detecting ranges. The target gas will only be identified when contact is made with the sensing element itself.

The AGSLPGTFT monitor should be installed approximately 1ft from ground level.

Find out more American Gas Safety LLC

www.americangassafety.com

Head office: 6304 Benjamin Road, Suite 502, Tampa, FL 33634

Tel: (727) 608-4375 Email: info@americangassafety.com