



NOTES:

- FOR PROJECTS WITH 25 AND 30-YEAR WARRANTIES OR WHEN USING 90-MIL MEMBRANE, ALL INSIDE CORNERS MUST BE OVERLAID WITH TWO LAYERS OF QUICK APPLIED FLASHING. THE BOTTOM LAYER SHALL BE A 7"x9" (178mm X 229mm) QUICK APPLIED PRE-CUT INSIDE/OUTSIDE CORNER OR A 6"x6" (152mm X 152mm) QUICK APPLIED UNCURED EPDM FLASHING PIECE COVERED WITH A 12"x12" TOP LAYER (305mm X 305mm) OF QUICK APPLIED UNCURED EPDM FLASHING. BOTH LAYERS SHALL BE CENTERED AND SEALED WITH CONTINUOUS LAP SEALANT.
- EPDM PRIMER MUST BE APPLIED TO ALL SPLICE AREAS AND FOR EACH LAYER OF QUICK APPLIED FLASHING.



INSIDE CORNER WITH CONTINUOUS EPDM WALL FLASHING

→ EPDM MEMBRANE

→ APPROVED SUBSTRATE

0 → SEE NOTE(S)

THERMOSET ROOFING SYSTEM

VGC-15.3