



CAUTION

PROJECTS WITH 20-YEAR WARRANTIES (MAXIMUM MEMBRANE THICKNESS 75-MIL), TAPE SPLICES MUST BE A MINIMUM 3" WIDE VERSIGARD QUICK APPLIED TAPE (QAT) OR A MINIMUM OF 6" FIELD APPLIED QA SEAM TAPE. REFER TO DETAIL VGC-2.1B FOR WARRANTY PROJECTS EXCEEDING 20-YEARS OR WHEN USING 90-MIL MEMBRANE.



MIN. 3" (76mm) WIDE QA SEAM TAPE IN CONJUNCTION WITH EPDM PRIMER



VERSIGARD QAT IN CONJUNCTION WITH EPDM PRIMER



DIMENSIONS	mm	
A 1/8"	3	TO
1/2"	13	MAX.



NOTES:

1. FIELD APPLIED QA SEAM TAPE IS TO BE OVERLAPPED A MINIMUM OF 1" (25mm) AT THE ENDS OF EACH CUT PIECE. APPLY LAP SEALANT AT TAPE OVERLAPS 2" (51mm) IN ALL DIRECTIONS AS SHOWN.
2. APPLY LAP SEALANT ALONG THE LEADING EDGE OF THE MEMBRANE SPLICE UNDER THE 6"X6" (152mm X 152mm) T-JOINT COVER, COVERING THE EXPOSED SPLICE TAPE 2" (51mm) IN ALL DIRECTIONS FROM THE SPLICE INTERSECTION.
3. 6" (152mm) WIDE QUICK APPLIED UNCURED EPDM FLASHING, IN CONJUNCTION WITH EPDM PRIMER, MAY ALSO BE CENTERED OVER THE INTERSECTING POINT OF THE LEADING EDGES OF THE FIELD SPLICE INTERSECTION.
4. LAP SEALANT IS REQUIRED ON CUT EDGES OF REINFORCED EPDM MEMBRANE.



EPDM MEMBRANE SPLICES

→ EPDM MEMBRANE
 → APPROVED SUBSTRATE
 → SEE NOTE(S)

THERMOSET ROOFING SYSTEM

VGC-2.1A