

PRE-MOLDED INSIDE CORNER BEFORE INSTALLATION


NOTES:

1. POSITION FASTENING PLATES 6" TO 9" (15 TO 23cm) FROM THE CORNER AND 1/2" TO 1" (1.5 TO 2.5cm) FROM EDGE OF MEMBRANE.
2. APPROXIMATELY 1/8" (0.5cm) DIAMETER BEAD OF CUT-EDGE SEALANT IS REQUIRED ON CUT EDGES OF REINFORCED TPO MEMBRANE.
3. REFER TO VERSICO SPECIFICATIONS FOR ACCEPTABLE VERSICO FASTENERS AND PLATES.
4. WHEN USING 60 OR 80-MIL MEMBRANE, APPLY A 4-1/2" (11cm) DIAMETER "T-JOINT" COVER AT ALL FIELD SPLICE INTERSECTIONS.

| DIMENSIONS | | cm | |
|------------|--------------------|-------|---------|
| (A) | 6" | 15 | APPROX. |
| (B) | 6"-9" | 15-23 | |
| (C) | 45-DEGREES APPROX. | | |



PRE-MOLDED INSIDE CORNER FLASHING



THERMOPLASTIC ROOFING SYSTEM

TPC-15.1