



BRICK GRILLE DETAIL




STRAIGHT LATTICE GRILLE DETAIL

MODEL	STANDARD MAX. VALUES	
	WIDTH	HEIGHT
600ADV	30' 4"	14' 4"



ELEVATION



SECTION B-B



SECTION A-A

PROJECTION	
MIN.	MAX.
12" X 14"	26" X 28"

ADVANCED ROLLING


600ADV ADVANCED PERFORMANCE SECURITY GRILLE

DWG. NO.	DATE:	Wayne Dalton.
SHEET	BY:	


COMPONENT	MATERIAL	OPERATION	NOTES:
HOOD	24 GA. GALVANIZED STEEL	MOTOR RH 208V 1-PHASE 60HZ VIA TRANSFORMER (190-207 V RANGE)	1. DIRECT DRIVE MOTOR ONLY
CURTAIN	GALVANIZED STEEL		
GUIDES	STEEL ANGLES		
BOTTOM BAR	ALUMINUM		

OPTIONS

OPENING WIDTH	
OPENING HEIGHT	
GUIDE OPTIONS	☐ ANGLE E ☐ ANGLE Z
GUIDE OPTIONS	☐ LATTICE ☐ BRICK
HOOD OPTIONS	☐ INTERIOR OCTAGON ☐ INTERIOR ROUND ☐ INTERIOR SQUARE ☐ EXTERIOR SLOPED



BRICK GRILLE DETAIL




STRAIGHT LATTICE GRILLE DETAIL


OPTIONS

OPENING WIDTH	
OPENING HEIGHT	
GUIDE OPTIONS	☐ ANGLE E ☐ ANGLE Z
GUIDE OPTIONS	☐ LATTICE ☐ BRICK
HOOD OPTIONS	☐ INTERIOR OCTAGON
	☐ INTERIOR ROUND
	☐ INTERIOR SQUARE
	☐ EXTERIOR SLOPED


MODEL	STANDARD MAX. VALUES	
	WIDTH	HEIGHT
600ADV	30' 4"	14' 4"



ELEVATION



SECTION A-A



SECTION B-B


PROJECTION	
MIN.	MAX.
12" X 14"	26" X 28"

ADVANCED ROLLING


600ADV ADVANCED PERFORMANCE SECURITY GRILLE

COMPONENT	MATERIAL	OPERATION	NOTES:
HOOD	24 GA. GALVANIZED STEEL	MOTOR LH 208V 1-PHASE 60HZ VIA TRANSFORMER (190-207 V RANGE)	1. DIRECT DRIVE MOTOR ONLY
CURTAIN	GALVANIZED STEEL		
GUIDES	STEEL ANGLES		
BOTTOM BAR	ALUMINUM		

DWG. NO.	DATE:	
SHEET	BY:	




BRICK GRILLE DETAIL



STRAIGHT LATTICE GRILLE DETAIL

OPTIONS	
OPENING WIDTH	
OPENING HEIGHT	
GUIDE OPTIONS	☐ ANGLE E ☐ ANGLE Z
GUIDE OPTIONS	☐ LATTICE ☐ BRICK
HOOD OPTIONS	☐ INTERIOR OCTOGON
	☐ INTERIOR ROUND
	☐ INTERIOR SQUARE
	☐ EXTERIOR SLOPED


MODEL	STANDARD MAX. VALUES	
	WIDTH	HEIGHT
600ADV	30' 4"	14' 4"



ELEVATION

SECTION B-B

PROJECTION	
MIN.	MAX.
12" X 14"	26" X 28"




SECTION A-A

ADVANCED ROLLING


COMPONENT	MATERIAL	OPERATION	NOTES:
HOOD	24 GA. GALVANIZED STEEL	MOTOR RH 230V 1-PHASE 60HZ VIA (208-245 V RANGE)	1. DIRECT DRIVE MOTOR ONLY
CURTAIN	GALVANIZED STEEL		
GUIDES	STEEL ANGLES		
BOTTOM BAR	ALUMINUM		

600ADV ADVANCED PERFORMANCE SECURITY GRILLE

DWG. NO.	DATE:	Wayne Dalton
SHEET	BY:	




BRICK GRILLE DETAIL




STRAIGHT LATTICE GRILLE DETAIL

OPTIONS	
OPENING WIDTH	
OPENING HEIGHT	
GUIDE OPTIONS	☐ ANGLE E ☐ ANGLE Z
GUIDE OPTIONS	☐ LATTICE ☐ BRICK
HOOD OPTIONS	☐ INTERIOR OCTOGON
	☐ INTERIOR ROUND
	☐ INTERIOR SQUARE
	☐ EXTERIOR SLOPED



ELEVATION

SECTION B-B



SECTION A-A

PROJECTION	
MIN.	MAX.
12" X 14"	26" X 28"


MODEL	STANDARD MAX. VALUES	
	WIDTH	HEIGHT
600ADV	30' 4"	14' 4"

ADVANCED ROLLING


COMPONENT	MATERIAL	OPERATION	NOTES:
HOOD	24 GA. GALVANIZED STEEL	MOTOR LH 230V 1-PHASE 60HZ VIA (208-245 V RANGE)	1. DIRECT DRIVE MOTOR ONLY
CURTAIN	GALVANIZED STEEL		
GUIDES	STEEL ANGLES		
BOTTOM BAR	ALUMINUM		

600ADV ADVANCED PERFORMANCE SECURITY GRILLE

DWG. NO.	DATE:	
SHEET	BY:	




BRICK GRILLE DETAIL



STRAIGHT LATTICE GRILLE DETAIL

MODEL	STANDARD MAX. VALUES	
	WIDTH	HEIGHT
600ADV	30' 4"	14' 4"



ELEVATION

SECTION B-B

PROJECTION	
MIN.	MAX.
12" X 14"	26" X 28"



SECTION A-A


ADVANCED ROLLING

600ADV ADVANCED PERFORMANCE SECURITY GRILLE


DWG. NO.	DATE:	
SHEET	BY:	

COMPONENT	MATERIAL	OPERATION	NOTES:
HOOD	24 GA. GALVANIZED STEEL	MOTOR RH 208V 3-PHASE 60HZ VIA TRANSFORMER (190-207 V RANGE)	1. DIRECT DRIVE MOTOR ONLY
CURTAIN	GALVANIZED STEEL		
GUIDES	STEEL ANGLES		
BOTTOM BAR	ALUMINUM		

OPTIONS	
OPENING WIDTH	
OPENING HEIGHT	
GUIDE OPTIONS	☐ ANGLE E ☐ ANGLE Z
GUIDE OPTIONS	☐ LATTICE ☐ BRICK
HOOD OPTIONS	☐ INTERIOR OCTAGON ☐ INTERIOR ROUND ☐ INTERIOR SQUARE ☐ EXTERIOR SLOPED




BRICK GRILLE DETAIL



STRAIGHT LATTICE GRILLE DETAIL

OPTIONS

OPENING WIDTH	
OPENING HEIGHT	
GUIDE OPTIONS	☐ ANGLE E ☐ ANGLE Z
GUIDE OPTIONS	☐ LATTICE ☐ BRICK
HOOD OPTIONS	☐ INTERIOR OCTAGON
	☐ INTERIOR ROUND
	☐ INTERIOR SQUARE
	☐ EXTERIOR SLOPED




ELEVATION



SECTION A-A

MODEL	STANDARD MAX. VALUES	
	WIDTH	HEIGHT
600ADV	30' 4"	14' 4"



SECTION B-B


PROJECTION	
MIN.	MAX.
12" X 14"	26" X 28"

ADVANCED ROLLING


600ADV ADVANCED PERFORMANCE SECURITY GRILLE

COMPONENT	MATERIAL	OPERATION	NOTES:
HOOD	24 GA. GALVANIZED STEEL	MOTOR LH 208V 3-PHASE 60HZ VIA TRANSFORMER (190-207 V RANGE)	1. DIRECT DRIVE MOTOR ONLY
CURTAIN	GALVANIZED STEEL		
GUIDES	STEEL ANGLES		
BOTTOM BAR	ALUMINUM		

DWG. NO.	DATE:	Wayne Dalton
SHEET	BY:	




BRICK GRILLE DETAIL




STRAIGHT LATTICE GRILLE DETAIL

OPTIONS	
OPENING WIDTH	
OPENING HEIGHT	
GUIDE OPTIONS	☐ ANGLE E ☐ ANGLE Z
GUIDE OPTIONS	☐ LATTICE ☐ BRICK
HOOD OPTIONS	☐ INTERIOR OCTOGON
	☐ INTERIOR ROUND
	☐ INTERIOR SQUARE
	☐ EXTERIOR SLOPED

MODEL	STANDARD MAX. VALUES	
	WIDTH	HEIGHT
600ADV	30' 4"	14' 4"



ELEVATION



SECTION B-B

PROJECTION	
MIN.	MAX.
12" X 14"	26" X 28"




SECTION A-A

ADVANCED ROLLING


COMPONENT	MATERIAL	OPERATION	NOTES:
HOOD	24 GA. GALVANIZED STEEL	MOTOR RH 230V 3-PHASE 60HZ VIA TRANSFORMER (208-245 V RANGE)	1. DIRECT DRIVE MOTOR ONLY
CURTAIN	GALVANIZED STEEL		
GUIDES	STEEL ANGLES		
BOTTOM BAR	ALUMINUM		

600ADV ADVANCED PERFORMANCE SECURITY GRILLE

DWG. NO.	DATE:	Wayne Dalton
SHEET	BY:	




BRICK GRILLE DETAIL




STRAIGHT LATTICE GRILLE DETAIL

MODEL	STANDARD MAX. VALUES	
	WIDTH	HEIGHT
600ADV	30' 4"	14' 4"



ELEVATION



SECTION B-B

PROJECTION	
MIN.	MAX.
12" X 14"	26" X 28"



SECTION A-A


ADVANCED ROLLING

600ADV ADVANCED PERFORMANCE SECURITY GRILLE


DWG. NO.	DATE:	Wayne Dalton
SHEET	BY:	

OPTIONS	
OPENING WIDTH	
OPENING HEIGHT	
GUIDE OPTIONS	☐ ANGLE E ☐ ANGLE Z
GUIDE OPTIONS	☐ LATTICE ☐ BRICK
HOOD OPTIONS	☐ INTERIOR OCTAGON ☐ INTERIOR ROUND ☐ INTERIOR SQUARE ☐ EXTERIOR SLOPED

COMPONENT	MATERIAL	OPERATION	NOTES:
HOOD	24 GA. GALVANIZED STEEL	MOTOR LH 230V 3-PHASE 60HZ VIA TRANSFORMER (208-245 V RANGE)	1. DIRECT DRIVE MOTOR ONLY
CURTAIN	GALVANIZED STEEL		
GUIDES	STEEL ANGLES		
BOTTOM BAR	ALUMINUM		



BRICK GRILLE DETAIL




STRAIGHT LATTICE GRILLE DETAIL


OPTIONS

OPENING WIDTH	
OPENING HEIGHT	
GUIDE OPTIONS	☐ ANGLE E ☐ ANGLE Z
GUIDE OPTIONS	☐ LATTICE ☐ BRICK
HOOD OPTIONS	☐ INTERIOR OCTAGON
	☐ INTERIOR ROUND
	☐ INTERIOR SQUARE
	☐ EXTERIOR SLOPED

MODEL	STANDARD MAX. VALUES	
	WIDTH	HEIGHT
600ADV	30' 4"	14' 4"



ELEVATION



SECTION B-B

PROJECTION	
MIN.	MAX.
12" X 14"	26" X 28"




SECTION A-A

ADVANCED ROLLING


600ADV ADVANCED PERFORMANCE SECURITY GRILLE

COMPONENT	MATERIAL	OPERATION	NOTES:
HOOD	24 GA. GALVANIZED STEEL	MOTOR RH 460V 3-PHASE 60HZ VIA TRANSFORMER (456-495V RANGE)	1. DIRECT DRIVE MOTOR ONLY
CURTAIN	GALVANIZED STEEL		
GUIDES	STEEL ANGLES		
BOTTOM BAR	ALUMINUM		

DWG. NO.	DATE:	
SHEET	BY:	



BRICK GRILLE DETAIL




STRAIGHT LATTICE GRILLE DETAIL


OPTIONS

OPENING WIDTH	
OPENING HEIGHT	
GUIDE OPTIONS	☐ ANGLE E ☐ ANGLE Z
GUIDE OPTIONS	☐ LATTICE ☐ BRICK
HOOD OPTIONS	☐ INTERIOR OCTOGON
	☐ INTERIOR ROUND
	☐ INTERIOR SQUARE
	☐ EXTERIOR SLOPED

MODEL	STANDARD MAX. VALUES	
	WIDTH	HEIGHT
600ADV	30' 4"	14' 4"




ELEVATION



SECTION B-B

PROJECTION	
MIN.	MAX.
12" X 14"	26" X 28"



SECTION A-A


ADVANCED ROLLING

600ADV ADVANCED PERFORMANCE SECURITY GRILLE


COMPONENT	MATERIAL	OPERATION	NOTES:
HOOD	24 GA. GALVANIZED STEEL	MOTOR LH 460V 3-PHASE 60HZ VIA TRANSFORMER (456-495V RANGE)	1. DIRECT DRIVE MOTOR ONLY
CURTAIN	GALVANIZED STEEL		
GUIDES	STEEL ANGLES		
BOTTOM BAR	ALUMINUM		

DWG. NO.	DATE:	Wayne Dalton.
SHEET	BY:	

MODEL	STANDARD MAX. VALUES	
	WIDTH	HEIGHT
600ADV	30' 4"	14' 4"




BRICK GRILLE DETAIL




STRAIGHT LATTICE GRILLE DETAIL

OPTIONS	
OPENING WIDTH	
OPENING HEIGHT	
GUIDE OPTIONS	☐ ANGLE E ☐ ANGLE Z
GUIDE OPTIONS	☐ LATTICE ☐ BRICK
HOOD OPTIONS	☐ INTERIOR OCTAGON
	☐ INTERIOR ROUND
	☐ INTERIOR SQUARE
	☐ EXTERIOR SLOPED




ELEVATION



SECTION B-B

PROJECTION	
MIN.	MAX.
12" X 14"	26" X 28"




SECTION A-A

ADVANCED
ROLLING


COMPONENT	MATERIAL	OPERATION	NOTES:
HOOD	24 GA. GALVANIZED STEEL	MOTOR RH 575 V 3-PHASE 60HZ	1. DIRECT DRIVE MOTOR ONLY
CURTAIN	GALVANIZED STEEL		
GUIDES	STEEL ANGLES		
BOTTOM BAR	ALUMINUM		

600ADV ADVANCED PERFORMANCE SECURITY GRILLE

DWG. NO.	DATE:	
SHEET	BY:	



BRICK GRILLE DETAIL




STRAIGHT LATTICE GRILLE DETAIL


OPTIONS

OPENING WIDTH	
OPENING HEIGHT	
GUIDE OPTIONS	☐ ANGLE E ☐ ANGLE Z
GUIDE OPTIONS	☐ LATTICE ☐ BRICK
HOOD OPTIONS	☐ INTERIOR OCTAGON
	☐ INTERIOR ROUND
	☐ INTERIOR SQUARE
	☐ EXTERIOR SLOPED

MODEL	STANDARD MAX. VALUES	
	WIDTH	HEIGHT
600ADV	30' 4"	14' 4"



ELEVATION



SECTION B-B

PROJECTION	
MIN.	MAX.
12" X 14"	26" X 28"



SECTION A-A

ADVANCED ROLLING

600ADV ADVANCED PERFORMANCE SECURITY GRILLE

COMPONENT	MATERIAL	OPERATION	NOTES:
HOOD	24 GA. GALVANIZED STEEL	MOTOR LH 575 V 3-PHASE 60HZ	1. DIRECT DRIVE MOTOR ONLY
CURTAIN	GALVANIZED STEEL		
GUIDES	STEEL ANGLES		
BOTTOM BAR	ALUMINUM		

DWG. NO.	DATE:	Wayne Dalton
SHEET	BY:	