


XYPEX PROJECT SPECIFICATIONS & SCHEMATIC DRAWINGS

BRIDGE



- ① APPLY ONE SLURRY COAT OF XYPEX CONCENTRATE TO STRUCTURAL SLAB AT THE RATE OF 1.5 LB./SQ. YD. (0.8 KG/M²)
- ② APPLY ONE SLURRY COAT OF XYPEX CONCENTRATE TO JOINT SURFACE BETWEEN PARAPET WALL AND BRIDGE DECK AT THE RATE OF 2.0 LB./SQ. YD. (1.0 KG/M²). XYPEX MUST BE APPLIED NO MORE THAN 24 HOURS PRIOR TO CONCRETE PLACEMENT.
- ③ APPLY A COVE STRIP OF XYPEX MODIFIED MORTAR OVER SLAB/WALL CONSTRUCTION JOINT SO THAT THE COVE EXTENDS ONE INCH (25 MM) UP THE WALL AND ONE INCH (25 MM) OUT ON TO THE DECK SURFACE.
- ④ APPLY ONE SLURRY COAT OF XYPEX CONCENTRATE TO WALL SURFACES AT THE RATE OF 1.5 LB./SQ. YD. (0.8 KG/M²)

SCHEMATIC DIAGRAM SHOWS XYPEX APPLICATION ONLY AND DOES NOT DEPICT THE STANDARD REQUIREMENTS FOR WATERSTOPS OR EXPANSION JOINT SEALANTS.

THE SPECIFIER CAN CONSIDER THE ALTERNATIVE USE OF XYPEX DRY SHAKE OR XYPEX ADMIX, WHERE APPLICABLE.

REFER TO STANDARD SPECIFICATIONS FOR FURTHER INFORMATION.