



DUDICK, INC.

Corporate Offices
1818 Miller Parkway
Streetsboro, OH 44241
330-562-1970
800-322-1970
330-562-7638 FAX
www.dudick.com

STERI-SEAL HB (High Build)

High Solids, Multi Functional, Spray Applied Pigmented High Build Chemically Resistant Epoxy Coating, For Ceiling & Wall Applications 30-40 Mil Thickness

GREEN BUILDING FEATURES

Low emitting material
Low VOC
Low installation odor
Processed and manufactured in Ohio

APPLICATION FEATURES

High Chemical & Abrasion Resistance
Excellent as a Ceiling & Wall Coating
USDA & FDA Compliant
Anti-Microbial Agents are available as an option

TYPICAL APPLICATIONS

Clean Rooms
Food & Beverage Processing Facilities
Warehouses/Storage Areas
Manufacturing & Waste Water Treatment Plants
Maintenance Garages Pharmaceutical & Research Facilities

CHEMICAL RESISTANCE

Dilute Inorganic Acids
Aliphatic Hydrocarbons
Sodium Hydroxide
Salt & Brine Solutions
Mineral Oils

*Please consult Dudick, Inc. for complete chemical resistance information.

SUBSTRATES

Concrete
CMU
Gypsum Board*
Cement Board*

*Consult Dudick, Inc. about exact procedure dependent on board characteristics.

COLORS: Available in Standard Floor Colors:

Light Gray Beige
Medium Gray Dark Blue
Dark Gray Light Blue
Tan Dark Green
Tile Red Light Green

Custom Colors Available, consult Dudick, Inc. for complete information.

* = Products are not reviewed or certified under the LEED Rating System. LEED credit requirements cover the performance of materials in aggregate, not the performance of individual products or brands. For more information on LEED, visit www.usgbc.org/leed.

TYPICAL PHYSICAL PROPERTIES

Taber Abrasion ASTM D4060	60 mg.
Specular Gloss Factor ASTM D523	85 – 90
Flame Spread ASTM D635	<5 mm / self extinguishing
Tensile Bond Strength ASTM D7234	Cohesive failure of concrete
Fungus Resistance	No growth
U.S. Mil Std. 810E	

SPECIFICATIONS

Steri-Seal HB shall be an epoxy coating applied in one or two 15-20 mil coats as manufactured by Dudick, Inc.

THE STERI-SEAL HB SYSTEM

Steri-Seal HB uses a moisture-tolerant primer and one or two coats of low odor epoxy resin to achieve high build and provide protection for concrete substrates. The unique hybrid binder in **Steri-Seal HB** provides high film integrity, and excellent chemical resistance required for prolonged substrate protection.

ESTIMATING QUANTITIES AND ORDER BILL OF MATERIAL

APPROXIMATE SQUARE FEET PER GALLON**	
PRIMER *See specified Primer Data Sheet	
STERI-SEAL HB	
1 st Coat	80-100 ft ² @ 15-20 mils
2 nd Coat	80-100 ft ² @ 15-20 mils

**Quantities shown are for estimating purposes only. Coverages will vary due to porosity of substrate.

APPLICATION INSTRUCTIONS SURFACE PREPARATION

Concrete: Concrete must be prepared mechanically to remove the surface laitance. Oils, grease or other contaminants must be removed prior to surface preparation. Concrete must be free of curing compounds and form release agents. Surface texture should be similar to 60-80 grit sandpaper or the visual standard, CSP-3 from the International Concrete Repair Institute. The prepared surface should have a nominal tensile strength of 250 PSI per ASTM D7234.

All concrete substrates must be checked for moisture prior to product application using the Plastic Sheet Test, ASTM D4263 or specified method.

Additional surface preparation will be required if a 60-80 grit texture is not achieved and the surface laitance not completely removed with the first mechanical preparation procedure.

CMU: Dudick, Inc. recommends CMU surfaces are lightly abrasive blasted to clean CMU block and to

provide a 60-80 grit sandpaper texture of the mortar joints. Care must be taken not to damage CMU.

Wall Boards: Consult Dudick, Inc. for preparation methods.

Mechanical preparation removes laitance, exposing honeycombs or voids beneath the surface that must be filled with ***Scratch-Coat**. (Refer to specified Dudick **Scratch-Coat** separate product bulletin).

ENVIRONMENTAL CONDITIONS

Temperature of the concrete substrate must be between 50°F and 110°F.

Relative humidity must not exceed 90%.

Substrate temperature must be 5°F above the Dew Point.

PRIMING

The following Primers are compatible with **Steri-Seal HB**: Primer 67, Primer 67LV, Primer 67DPLV, Primer 67DTO & Primer 60.

STERI-SEAL HB MIX RATIO (BY VOLUME)

Component A 1 gallon
Component B 48 fl. oz.

Steri-Seal HB Pot Life & Cure Time

Temperature	Work Life	Cure Time	Recoat	
			Min.	Max.
50°F	75 min.	96 hrs.	16-18 hrs.	120 hrs.
75°F	50 min.	24 hrs.	10-12 hrs.	72 hrs.
90°F	25 min.	20 hrs.	6-8 hrs.	48hrs.



DUDICK, INC.

Corporate Offices
1818 Miller Parkway
Streetsboro, OH 44241
330-562-1970
800-322-1970
330-562-7638 FAX
www.dudick.com

STERI-SEAL HB (High Build)

High Solids, Multi Functional, Spray Applied Pigmented High Build Chemically Resistant Epoxy Coating, For Ceiling & Wall Applications
30-40 Mil Thickness

Prior to adding the **Component B**, mechanically mix the **Steri-Seal HB Component A** separately for 1-2 minutes to disperse any pigments or fillers which have settled.

Add the correct amount of **Component B** and mix until a uniform color is achieved. Spray apply the first coat evenly to 15-20 mils WFT.

Apply a second coat of **Steri-Seal HB** after the first coat has cured tack free, (approximately 10 hours at 75° F).

Consult Dudick representative for recommendation for spray application.

*If re-coat times are exceeded, contact your Dudick, Inc. representative.

Important - With all epoxies after priming and before each additional coat, examine the surface for amine blush (oily film). If present, remove by washing with warm water and detergent.

The pot life of **Steri-Seal HB** system components will depend upon the temperature. To prevent material waste and avoid damage to equipment, do not mix more material than can be used according to the Work Life & Cure Time charts.

Do not attempt to store mixed material. Residual material should be properly disposed of at the end of each work period.

Application of **Steri-Seal HB** in direct sunlight may lead to blistering, pinholes, or wrinkling due to outgassing of air in the concrete and high substrate temperatures. Double priming, shading or evening application may be required. Consult a Dudick

representative. **Steri-Seal HB** system is intended for interior use only.

OPTIONAL SEALERS

For **improved** UV stability, abrasion, stain resistance and chemical resistance. A Sealer can be applied over **Steri-Seal HB**. Consult Dudick for best options.

CLEAN UP

Use **S-10 Cleaning Solvent** to clean tools and equipment.

SHIPPING

Refer to Material Safety Data Sheets.

STORAGE

Warning: All Dudick products classified by DOT with white, yellow or red labels must not be mixed or stored together as an explosive reaction can occur.

All products should be stored in a cool, dry area, away from open flames, sparks, or other hazards. When properly stored in their original, unopened containers at 50°F-75°F, **Steri-Seal HB** components will have a twelve-month shelf life. Storage in direct sunlight or excessive heat will reduce working time and shelf life.

SAFETY

M.S.D.S: Material Safety Data Sheets must always be read before using products. **Steri-Seal HB** is intended for application by experienced, professional personnel. Dudick, Inc. can supply

supervision to help determine that the surface has been properly prepared, the ingredients correctly mixed, and the materials properly and safely applied.

If **Steri-Seal HB** materials are to be applied by your own personnel or by a third party contractor, please be sure that they are aware of the following safety precautions:

- Exposure to resins and hardeners through direct skin contact and/or inhalation may cause severe dermatitis reactions in some people. Cleanliness of the skin and clothing is critical and must be of paramount concern.
- Fumes are flammable and heavier than air. Proper ventilation should be maintained to minimize breathing of concentrated fumes.
- Suitable respirators should be used during application.
- Safety glasses, gloves, and suitable protective clothing must be worn at all times during application.
- If contact with hardeners occurs, remove any clothing involved and flush the skin with flowing water. Discard the clothing. Do not attempt to wash and reuse it. **Steri-Seal HB** liquid can be removed with **S-10 Cleaning Solvent, MEK, or Acetone**.
- Keep open flames and sparks away from the area where materials are being mixed and applied.
- If a rash occurs, remove the individual from the work area and seek a physician's care for dermatitis.
- In case of eye contact, flush with water for at least 15 minutes and consult a physician.
- If swallowed, do not induce vomiting; call a physician immediately.

NOTE: Dudick, Inc. ("Dudick") warrants all goods of its manufacture to be as represented in its catalogs and that the manufacture of its products by its

employees or sub-contractors shall be performed in a workmanlike manner. Dudick's sole obligation under this warranty shall be to replace any material which its examination shall disclose to be defective. Dudick makes no warranty concerning the suitability of its product for application to any surface, it being understood that the goods have been selected and the application ordered by the

Purchaser. DUDICK, INC. MAKES NO WARRANTY, EXPRESS OR IMPLIED, THAT THE GOODS SHALL BE MERCHANTABLE OR THAT THE GOODS ARE FIT FOR ANY PARTICULAR PURPOSE. THE WARRANTY OF REPAIR OR REPLACEMENT SET FORTH HEREIN IS EXCLUSIVE AND IN LIEU OF ALL OTHER WARRANTIES ARISING BY LAW OR OTHERWISE; AND DUDICK INC. SHALL NOT BE LIABLE FOR INCIDENTAL OR CONSEQUENTIAL DAMAGES, INCLUDING BUT NOT LIMITED TO LOST PROFITS, DOWN TIME, DAMAGES TO PROPERTY OF THE PURCHASER OR OTHER PERSONS, OR DAMAGES FOR WHICH THE PURCHASER MAY BE LIABLE TO OTHER PERSONS,

WHETHER OR NOT OCCASIONED BY DUDICK'S NEGLIGENCE. This warranty shall not be extended, altered or varied except by written instrument signed by Dudick and Purchaser.

11/18/22