

# TEST REPORT

Report No. : MAN:HL:1548001381

ISSUE DATE: 23-Mar-2024



## GARWARE HI-TECH FILMS LIMITED

WALUJ MIDC AREA, AURANGABAD PUNE  
ROAD CHHATRAPATI SAMBHAJINAGAR- 431133  
INDIA

CONTACT PERSON: P K NAIKNAWARE

## THE FOLLOWING SAMPLE(S) WAS/WERE SUBMITTED AND IDENTIFIED BY/ON BEHALF OF THE CUSTOMER AS :

SAMPLE DESCRIPTION	DUAL REFLECTIVE LAMINATE – DUAL REFLECTIVE CHARCOAL 15 FILM
MATERIAL DISCRPTION	DR-CH15 2.0M TSD SRA GR UCD BO N AMS
LABEL ON ROLL	DEFENDO CHARCOAL 15
COLOUR	CHARCOAL
STYLE NO.	DEFENDO CHARCOAL 15
ORDER NO.	2300014202 / WSC
SKU NO.	08
END USE	APPLICATION ON GLASS WINDOWS
COUNTRY OF DESTINATION	INDIA
COUNTRY OF ORIGIN	INDIA

## LAB PROVIDED DETAILS:

CONDITION OF SAMPLE COMPLETE AND OK

THE LOCATION OF PERFORMANCE OF THE LABORATORY ACTIVITIES: SGS CHINA LABORATORY

SAMPLE RECD ON 17-Feb-2024 TESTING PERIOD : 17-Feb-2024 - 23-Mar-2024

## SUMMARY OF TEST RESULTS:

TESTS	PASS	FAIL	REMARKS
ASTM E84-23C STANDARD TEST METHOD FOR- SURFACE BURNING CHARACTERISTICS-BUILDING MATERIALS			SEE RESULT

Remarks: P=Pass

F=Fail

TEST(S) RESULT & METHOD: PLEASE REFER TO NEXT PAGE(S). RESULTS APPLY TO THE SAMPLE AS RECEIVED

Per Pro SGS India Pvt. Ltd.



SANDIP BHUSHAN  
TECHNICAL MANAGER

Authorized Signatory-Mechanical

Email your Test Report Related Enquiries at [Feedback.HLT@sgs.com](mailto:Feedback.HLT@sgs.com)

## TEST REPORT

Report No. : MAN:HL:1548001381

ISSUE DATE: 23-Mar-2024



NON ACCREDITED TEST(S)

### TEST RESULT:

#### SURFACE BURNING CHARACTERISTICS-BUILDING MATERIALS:-

#### I. Test Conducted

This test was conducted in accordance with ASTM E84-23c Standard Test Method for Surface Burning Characteristics of Building Materials.

#### II. Introduction

The method, designated as ASTM E84-23c, "Standard Method of Test for Surface Burning Characteristics of Building Materials", is designed to determine the relative surface burning characteristics of materials under specific test conditions. Results are expressed in terms of flamespread index (FSI) and smoke developed index (SDI).

The purpose of this test method is to determine the relative burning behavior of the material by observing the flame spread along the specimen. Flame spread and smoke developed index are reported. However, there is not necessarily a relationship between these two measurements.

#### III. Test Procedure

The tunnel is preheated to 65.6°C(150°F), as measured by the floor-embedded thermocouple located 7.09m (23.25 ft) downstream of the burner ports, and allowed to cool to 40.6°C(105°F), as measured by the floor-embedded thermocouple located 3.96m (13 ft) from the burners. At this time the tunnel lid is raised and the test sample is placed along the ledges of the tunnel so as to form a continuous ceiling 7.32m (24 ft) long, 304.8mm (12 in) above the floor. The lid is then lowered into place.

Upon ignition of the gas burners, the flame spread distance is observed and recorded every 30 seconds. Flame spread distance versus time is plotted ignoring any flame front recessions. If the area under the curve (A) is less than or equal to 97.5 ft\*min, FSI = 0.515·A; if greater, FSI = 4900/(195-A).

The test results for smoke shall be plotted and the area under the curve shall be divided by the area under the curve for heptane, multiplied by 100, and rounded to the nearest multiple of five to establish a numerical smoke-developed index (SDI).

#### IV. Conditioning

Prior to testing, the sample was conditioned to a constant weight at a temperature of (23±2.8)°C(73.4±5)°F and at a relative humidity of (50±5)%.

## TEST REPORT

Report No. : MAN:HL:1548001381

ISSUE DATE: 23-Mar-2024



NON ACCREDITED TEST(S)

### Sample Details

Sample description	Film
Sample size	2400mmx510mm
Thickness	0.05mm

**Exposed face:** Smooth surface

### Mounting methods:

The test specimen was pasted on the fiber-cement board by adhesive (RUBSTIK TROPIC 2335) and fiber-cement board with a density is 1440kg/m<sup>3</sup>. The test specimen consisted of a total 3 sections of material. Thesections were butted together during testing to form the required specimen length.

### Test results:

Flame Spread Index, FSI	Smoke-developed Index, SDI
10	30

### Rating:

The National Fire Protection Association Life Safety Code 101, Chapter 10, Section 10.2.3 "Interior Wall and Ceiling Finish Classification", has a means of classifying materials with respect to Flame Spread and Smoke Developed when tested in accordance with ASTM E84, UL 723 "Method of Test of Surface Burning Characteristics of Building Materials".

International Building Code, Chapter 8, Interior Finishes, Section 803 "Wall and Ceiling Finishes", was classified in accordance with ASTM E84 or UL 723. Such interior finish materials shall be grouped in the following classes in accordance with their flame spread and smoke-developed indexes.

### The classifications are as follows:

Classification	Flame Spread Index, FSI	Smoke-developed Index, SDI
Class A	0-25	0-450
Class B	26-75	0-450
Class C	76-200	0-450

Since the tested sample received a Flame Spread Index 10 and a Smoke-developed Index 30, it **would meet** the requirements of **Class A** interior Wall & Ceiling Finish Category.

JOE No. : 2448800720

400197566

Page 3 of 5

Control No.: 1548002122

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <http://www.sgs.com/terms> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at [www.sgs.com/terms\\_e-document.htm](http://www.sgs.com/terms_e-document.htm). Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. The laboratory shall be responsible for all the information provided in the report, except when information and instruction for specific scope of testing is provided by the customer. "Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only. No decision rule is applied, when comparing the measurement result (s) with the applicable limit(s) according to the specification in the respective standard or as shared by the customer.

## TEST REPORT



Report No. : MAN:HL:1548001381

ISSUE DATE: 23-Mar-2024



NON ACCREDITED TEST(S)

### Graphical Results:



JOE No. : 2448800720

400197566

Page 4 of 5

Control No.: 1548002122

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <http://www.sgs.com/terms> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at [www.sgs.com/terms\\_e-document.htm](http://www.sgs.com/terms_e-document.htm). Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. The laboratory shall be responsible for all the information provided in the report, except when information and instruction for specific scope of testing is provided by the customer. "Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only. No decision rule is applied, when comparing the measurement result (s) with the applicable limit(s) according to the specification in the respective standard or as shared by the customer.

# TEST REPORT

Report No. : MAN:HL:1548001381

ISSUE DATE: 23-Mar-2024



NON ACCREDITED TEST(S)

## Observations

Time to ignition (sec)	10
Time to Max. FS (sec)	60
Maximum FS (feet)	2.0
Observations	Non-flaming Debris

## Warning:

The use of supporting materials on the underside of the test specimen has the ability to lower the flame spread index from those which might be obtained if the specimen could be tested without such support. These test results do not necessarily relate to indices obtained by testing materials without such support. Testing of materials that melt, drip, or delaminate to such a degree that the continuity of the flame front is destroyed, results in low flame spread indices that do not relate directly to indices obtained by testing materials that remain in place.

The test results relate only to the specimens of the product in the form in which were tested. Small differences in the composition or thickness of the product may significantly affect the performance during the test and may therefore invalidate the test results. Care should be taken to ensure that any product, which is supplied or used, is fully represented by the specimens, which were tested.

## Statement:

This declaration of conformity is only based on the result of this laboratory activity, the impact of the uncertainty of the results was not included.

## Note:

This document cannot be reproduced except full, without prior written approval of the Company.  
Test has been sub-contracted to ISO/IEC 17025 accredited laboratory.

## Photo Appendix:



SGS authenticate the photo on original report only

\*\*\*\*\*END OF REPORT\*\*\*\*\*

JOE No. : 2448800720

400197566

Page 5 of 5

Control No.: 1548002122

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <http://www.sgs.com/terms> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at [www.sgs.com/terms\\_e-document.htm](http://www.sgs.com/terms_e-document.htm). Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. The laboratory shall be responsible for all the information provided in the report, except when information and instruction for specific scope of testing is provided by the customer. "Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only. No decision rule is applied, when comparing the measurement result (s) with the applicable limit(s) according to the specification in the respective standard or as shared by the customer.