


M4.10-N30 TILE NOSING

The M4.10-N30 Photoluminescent Tile nosing has been designed specifically for tiled stair installations. By taking the classic benefits of Ecoglo® step edge definition, slip resistance and wear resistance and combining it with a refined and durable anodized aluminum profile, the M4 series nosing offers strength, beauty and peace of mind to any tiled stair.



ENGINEERED FOR DURABILITY

- The hard-wearing silicon carbide non-slip material is integrally bonded to the aluminum substrate. Thousands of people can walk on it with no signs of wear and tear.
- The thick anodized finish is aesthetically pleasing, prevents corrosion, and is extremely hard and abrasion resistant. The anodized aluminum surface is harder than pure aluminum, second only to diamonds hard crystalline structure.

STEP EDGE SAFETY

- The color contrasting the non-slip material provides excellent step edge visibility.

GENERAL INFORMATION

- Available in 8ft lengths.
- Product is sold with inserts unattached. The aluminum extrusion is cut using a saw with a blade for cutting non-ferrous metals. For best results, we recommend cutting inserts with a shear.
- Inserts are installed into aluminum nosing using a premium polyurethane adhesive (not included).

ENVIRONMENTALLY FRIENDLY

- LEED points qualified
- Recyclable; No disposable cost

ALUMINUM FINISH

- Available in Clear Anodized Aluminum Finish.
- Black, Light Bronze and Dark Bronze Anodize finishes are available at additional cost.

PRODUCT COLORS




Black
M4170.10

Grey
M4160.10

Yellow
M4150.10

PRODUCT DIMENSIONS



*The M4.10 tile nosing profile is compatible with tiles that are between 3/16" and 11/32" (5mm and 8.5mm) thick.



SA33553
4HT0
UL 1994 AND
ULC 572 LISTED



BIMready

ecoglo®
VISIBLY BETTER

M4.10-N30 TILE NOSING

QUALIFIES FOR LEED POINTS

MR Credit 2: Construction Waste Management Divert from Land Fill

- Products are Aluminum based and 100% recyclable.

MR Credit 4: Recycled Content

- Products are Aluminum based and approximately 20% of the aluminum content in an Ecoglo secondary billet specification is recycled scrap. Ecoglo's Recommended Installation Adhesive for low VOC's and qualifies for Indoor Environmental Quality credits for low emitting materials: EQc4.1

BENEFITS AND TECHNICAL DETAILS: Ecoglo M4.10-N30 meets or exceeds the performance criteria specified in the following tests or standards:

UV STABILITY

High durability indoors and outdoors.

- ASTM G155-04 Cycle 1 2000hrs, Standard Practice for Operating Xenon Arc Light Apparatus for Exposure of Nonmetallic Materials.
- Salt Spray Resistance: ASTM B117-97 500hrs, Standard Practice for Operating Salt Spray (Fog) Apparatus.
- Freeze-Thaw Resistance: ASTM C1026-87(1996), Standard Test Method for Measuring the Resistance of Ceramic Tile to Freeze-Thaw Cycling

SLIP RESISTANT

Reduces slips.

- UL410, Standard for Slip Resistance for Floor Surface Materials.
- AS/NZS 4586-1999, Slip Resistance Classification of New Pedestrian Surface Materials.

ABRASION RESISTANCE

Hard wearing.

- ASTM D1242-95a, Standard Test Methods for Resistance of Plastic Materials to Abrasion.
- ASTM F510-93(2004), Standard Test Method for Resistance to Abrasion of Resilient Floor Coverings Using an Abrader with a Grit Feed Method.
- JIS H8682-1:1999, Test methods for abrasion resistance of anodic oxide coatings on aluminum and aluminum alloys- Wheel wear test.

WASHABILITY

Easy Cleaning.

- ASTM D4828-94(2003), Standard Test Methods for Practical Washability of Organic Coatings.

FLAMMABILITY

Does not burn.

- ASTM E162-02, Standard Test Method for Surface Flammability of Materials Using a Radiant Heat Energy Source.
- ASTM D635-03, Standard Test Method for Rate of Burning and/or Extent and Time of Burning of Plastics in a Horizontal Position.
- FAA AC 23.2 Paragraph 4.b, Horizontal Burn Test.

CONTACT ECOGLO INC. FOR A QUICK QUOTE OR TO OBTAIN MORE INFORMATION ABOUT OUR EMERGENCY LIGHTING PRODUCTS.

MADE IN USA