

Features and Components

- Use:** For field seaming JM White EPDM membranes. Utilizes a clear polyethylene release liner for ease of installation.
- Materials:** 3" or 6" (7.62 cm or 15.24 cm) wide, self-adhering, extruded White EPDM (ethylene propylene diene monomer) with a clear polyethylene release liner.
- Color:** White



Component

A
Accessory

Single Ply

Type

MS
Membrane Seaming

System Compatibility

This product may be used as a component in the following systems. Please reference product application for specific installation methods and information.

Multi-Ply	BUR			APP			SBS		
	HA	CA	HW	HA	CA	HW	SA	MF	
									Do not use in Multi-Ply systems

Key: HA = Hot Applied CA = Cold Applied HW = Heat Weldable SA = Self Adhered

Single Ply	TPO				PVC			EPDM		
	MF	AD	SA	IW	MF	AD	IW	MF	AD	BA
										Compatible with the selected Single Ply systems above

MF = Mechanically Fastened IW = Induction Weld BA = Ballasted AD = Adhered

Peak Advantage® Guarantee Information

Systems
Approved for use in certain JM Peak Advantage Guarantee Systems.

Installation/Application



Self-Adhered

- Prime White EPDM membrane with JM Single Ply Membrane Primer - LVOC or TPO Membrane Primer before applying to JM White EPDM Seam Tape Plus.
- Do not install in direct contact with asphalt or coal tar pitch.
- Refer to JM White EPDM applicator guides or detail drawings for instructions.

Packaging and Dimensions

Roll Sizes	3" x 100' (7.62 cm x 30.48 m)	6" x 100' (15.24 cm x 30.48 m)
Thickness	0.030" (0.76 mm)	
Roll Coverage	25 ft² (2.33 m²)	50 ft² (4.65 m²)
Rolls per Box*	4	2
Linear Units per Box	400 lin ft (121.92 lin m)	200 lin ft (60.96 lin m)
Weight per Box	24 lb (10.89 kg)	25 lb (11.34 kg)

*Each box of JM EPDM Seam Tape Plus includes scrubber pads and handle for seam priming.

Storage

Shelf Life	18 months from manufacture date
Storage Conditions	Store indoors, out of direct sunlight, and keep clean and dry prior to application.
Temperature Range	60°F – 80°F (16°C – 27°C)

Technical specifications as shown in this literature are intended to be used as general guidelines only. Please refer to the Safety Data Sheet and product label prior to using this product. The Safety Data Sheet is available by calling (800) 922-5922 or on the web at www.jm.com/roofing. The physical and chemical properties of the product listed herein represent typical, average values obtained in accordance with accepted test methods and are subject to normal manufacturing variations. They are supplied as a technical service and are subject to change without notice. Check with the regional sales representative nearest you for current information.

All Johns Manville products are sold subject to Johns Manville's standard Terms and Conditions, which includes a Limited Warranty and Limitation of Remedy. For a copy of the Johns Manville standard Terms and Conditions or for information on other Johns Manville roofing products and systems, visit www.jm.com/terms-conditions.