SOUND ABSORPTION MADE EASY!

Poly Max[™] Cloud

Poly Max polyester acoustical Cloud panels are nonallergenic, non-toxic, fungal-resistant, and do not contain chemical irritants or formaldehyde. Decorative and tackable, apply the acoustically absorbent Cloud panels to ceilings to tame echo and reverberation. Available in a variety of colors or printed with custom graphics to blend into any décor. Material: 100% polyester (60% PET-recycled fiber, 40% PET-virgin fiber)

APPLICATIONS:

Theaters, gymnasiums & multipurpose rooms, commercial & office buildings, studios & production houses, pro audio, restaurants & night clubs, government & municipal buildings, hospitals & medical clinics, schools & universities, houses of worship, industrial & manufacturing facilities and much more.

SIZES & OPTIONS

Standard Sizes: 24" x 48", 48" x 96" Cut To Size/Custom Up to 48" x 96" Thickness/Density: 1" thick/7.5 lb. pcf; 2" thick/5 lb. pcf

COLORS



Printed Graphics available, call for information

ACOUSTICAL PERFORMANCE

ASTM C423 A-Mount: 1": 0.70 NRC; 2": 0.95 NRC

FLAMMABILITY

Class A Fire-Rated per ASTM E84





INSTALLATION

To install ASI suspended Poly Max panels, loop suspension cable (by installer) through factory installed eyelet in panel and close the loop with a cable clamp or similar hardware. Anchor suspension cable to the roof deck or ceiling structure as necessary.



Building Knowledge Improving Project Delivery

ACOUSTICAL SURFACES, INC.

© 2020 Acoustical Surfaces, Inc. V1

Celebrating Over 35 Years – SOUNDPROOFING, ACOUSTICS, NOISE & VIBRATION SPECIALISTS 952.448.5300 | 800.448.0121 | sales@acousticalsurfaces.com | www.acousticalsurfaces.com