

Features and Components

- Use:** Asphalt bleed-out coverage or aesthetic touch ups on modified bitumen and built-up cool roof coated cap sheets.
- Type:** One-part, acrylic elastomeric seam coating.
- Color:** White
- Features:** Asphalt bleed blocking.
Improved aesthetic appearance.
Energy savings.
Prolonged roof life.
Reduced life cycle costs.



System Compatibility This product may be used as a component in the following systems. Please reference product application for specific installation methods and information.

Multi-Ply	BUR		APP		SBS			
	HA	CA	CA	HW	HA	CA	HW	SA
Compatible with all Multi-Ply systems								

Single Ply	TPO		PVC		EPDM		
	MF	FA	MF	FA	MF	FA	BA
Do not use in Single Ply systems							

Key: HA = Hot Applied CA = Cold Applied HW = Heat Weldable SA = Self Adhered MF = Mechanically Fastened FA = Fully Adhered BA = Ballasted

Energy and the Environment

CRRC®	Initial	Reflectivity: 0.76	Emissivity: 0.85
	Weathered	Reflectivity: 0.61	Emissivity: 0.92
	Rated Product ID: 0662-0007		Licensed Manufacturer ID: 0662
Classification: Production Line			
LEED®	SRI	92	
	Recycled Content	0%	
VOC	17 g/L (max.)		ENERGY STAR

* Cool Roof Rating Council ratings are determined for a fixed set of conditions, and may not be appropriate for determining seasonal energy performance. The actual effect of solar reflectance and thermal emittance on building construction may vary. Manufacturer of product stipulates that these ratings were determined in accordance with the applicable Cool Roof Rating normal procedures.

Installation/Application



- Apply when temperature is 50°F (10°C) and rising. Do Not Thin.
- Please refer to detailed installation instructions on next page.

Packaging and Coverage

Container Size	5 gal (18.9 l) pail
Shipping Weight (approx.)	60 lb [27.2 kg]
Coverage Rate*	Fiber Glass Felts: 65 - 100 ft ² /gal (1.60 - 2.45 m ² /l)
	Smooth-surfaced Modified Sheets: 65 - 100 ft ² /gal (1.60 - 2.45 m ² /l)
	Mineral-surfaced BUR/modified Sheets: 50 - 70 ft ² /gal (1.23 - 1.72 m ² /l)

* Coverage, open and dry time rates can vary dramatically depending on the particular substrate and environmental conditions. Coverage rates stated herein are approximate only. If FM Global® or UL® approval is required, consult specific RoofNavSM or the UL Certifications Directory for specific application rates.

Storage

Shelf Life	12 months from manufacture date (unopened pail)
Storage Conditions	Clean, dry, indoor environment in an unopened or tightly sealed container.
Temperature Range	40°F – 100°F (4°C – 38°C) - Protect from freezing



JM CR SEAM COATING

Installation/Application Instructions

For best results, apply this product on roofing membranes that have cured for 60 days or longer.

Use a brush, roller or spray equipment to apply JM CR Seam Coating. All surfaces must be clean, dry and free of any dirt, grease, oil or other debris that may interfere with proper adhesion. If multiple applications are needed, the first coat should be completely dry (normally 4 to 12 hours) before applying the subsequent coats.

Temperatures must be 50°F (10°C) and rising during time of application. Do not apply JM CR Seam Coating within 24 hours of anticipated rain, dew or freezing temperatures. As with any coating, cooler temperatures and high humidity will slow the cure time. Coating should be applied under normal environmental conditions without thinning. All equipment can be cleaned with water and heavy duty detergent.

Precautions

Avoid prolonged contact with skin • Avoid contact with eyes • Do not take internally • Keep container closed when not in use • Keep out of reach of children.