




TECHNICAL DATA SHEET

Steel-X #12-14 Self-Driller

- 5/16" Hex Head
- 60° Rolled Threads
- Zinc Plated
- #3 Self-Drill Point
- EDPM Bonded Sealing Washer
- L3 Dura Protec™ Coating

DIMENSIONAL PROPERTIES:

- A - .308"
 - B - .551" (14 mm)
 - C - .414"
 - D - .212" Major
 - E - .160" Minor
- (Nominal Values)



MECHANICAL PROPERTIES

Material (Carbon Steel):	1022
Tensile Strength (min. LBr):	3105
Torsional Strength (min. LBin):	152
Shear Strength (min LBr):	2100
Hardness (HV):	590

PULLOUT VALUES (Average LBr)

29 Gauge	131 LBr
26 Gauge	202 LBr
22 Gauge	306 LBr
20 Gauge	359 LBr
16 Gauge	822 LBr
14 Gauge	1105 LBr
12 Gauge	1681 LBr

CORROSION PERFORMANCE

SALT SPRAY (ASTM B117)	1,500 Hrs.*
0% Visible Red Rust	*L3 Dura Protec™

Technical data provided herein is to be used as a guide for typical strength characteristics only.

DISCLAIMER: ALL TEST RESULTS CONTAINED WITHIN THIS DOCUMENT ARE BASED ON LABORATORY CONDITIONS, SPECIFIC JOB SITE CONDITIONS, AND SHOULD BE TAKEN INTO CONSIDERATION WHEN SPECIFYING THE PROPER FASTENER. BECAUSE APPLICATION CONDITIONS VARY, WE ASSUME NO LIABILITY FOR THE USE OF THIS INFORMATION.

