

CD-5080-F

DUCT DOOR for Fiberglass Ducts

Application

- Economical access to fiberglass ducts

Product Features

- These doors are for use in low to medium pressure fiberglass ducts
- Double cam - no hinge, removable door panel

Options:

- Aluminum, stainless steel

CD-5080-F Duct Access Door Specifications:

Material: Galvanized steel

Door: 24 gauge

Mounting Frame: 24 gauge

Gasketing: 1/8" thick by 1/2" wide closed cell neoprene gasketing between door and frame. 1/16" thick by 1 1/2" adhesive bonded gasket between frame to duct

Insulation: 2" of Fiberglass Insulation Compressed to 1" 7.7R Value

Latch: Self tightening, hand operated cam latch



CD-5080-F STANDARD SIZES

(other sizes available upon request)

Nominal Door Size W&H		Latches	Weight per Door	
Inches	mm		lbs.	kg.
6 x 6	152 x 152	2	1.0	0.5
8 x 8	203 x 203	2	1.25	0.6
10 x 10	254 x 254	2	2.0	0.9
12 x 12	304 x 304	2	2.5	1.1
14 x 14	356 x 356	4	3.25	1.5
16 x 16	406 x 406	4	4.0	1.8
18 x 18	457 x 457	4	5.5	2.5
20 x 20	508 x 508	4	9.0	4.1
24 x 24	610 x 610	4	12.0	5.4

Duct opening is same size as normal door opening

For detailed specifications see submittal sheet

