

# PS-5030

## FLUSH ACCESS DOOR for plaster walls & ceilings

### Application

- Installation in plaster walls and ceilings, before the plaster is applied

### Product Features

- An expansion casing bead with 3" wide galvanized lath
- Concealed continuous hinge

### PS-5030 Access Door Specifications:

**Material:** Door / Door Frame: 14 gauge

**Mounting Frame:** Formed door panel, flanged on four sides, flush to edge of frame expansion casing bead with 3" wide galvanized lath, recessed 3/4" to receive plaster

**Hinge:** Continuous, concealed

**Standard Latch:** Stainless Steel Slotted Screwdriver Cam Latch

**Optional Latches/Locks:** Cylinder lock & key, allen head cam latch, spanner head cam latch, torx

**Finish:** Baked White Prime Coat

(Additional finish paint is recommended for superior corrosion resistance)

### PS-5030 STANDARD SIZES

(other sizes available upon request)

Nominal Door Size W&H		Latches	Weight per Door	
Inches	mm		lbs.	kg.
8 X 8	203 X 203	1	2.3	1.0
10 X 10	254 X 254	1	4.3	2.0
12 X 12	305 X 305	1	6.3	2.9
14 X 14	355 X 355	1	6.5	2.9
16 X 16	406 X 406	2	10.1	4.6
18 X 18	457 X 457	2	12.1	5.5
22 X 22	560 X 560	4	16.4	7.4
24 x 24	610 x 610	4	19.4	8.8
24 X 36	610 X 914	5	37.2	16.9

Wall opening is W + 3/8" (9 mm)

For detailed specifications see submittal sheet

