

# Technical Data Sheet Signature 843-E

Signature 80

С О

Serie

## Features & Options

#### **Standard Features**

- Electrically-operated continuously-hinged movable partition.
- Driven by #35 roller chain.
- STC 43 or 47 with gypsum board faces.
- STC 49, 52, 53 and 55 with steel faces laminated to gypsum board.
- 102 mm [4"] nominal thickness. 1230 mm [48 1/2"] maximum width.
- Clear-anodized steel-reinforced aluminum frame.
- Protective trims on entire perimeter.
- Combination aluminum and vinyl tongue and groove vertical sound seals between panels.
- Final closure by lateral wall jamb.
- Low profile steel hinges.
- Clear-anodized 6063-T6 alloy aluminum track.
- Each panel supported by one 4-wheeled carrier with steel tires over hardened steel ball bearing wheels.
- · Vinyl wallcovering.

- Type FF horizontal seals :
  - Fixed top and bottom sweeps
  - bottom seals provide a 50 mm [2"] floor clearance
  - standard for STC 43, 47, 49 and 52
  - not available for STC 53 and 55
- Type FA horizontal seals:
  - Fixed top sweeps
  - Automatic retractable bottom seals set as panels are deployed
  - bottom seals provide a 50 mm [2"] floor clearance
  - standard for STC 53 and 55
  - optional for STC 43, 47, 49 and 52
- Maximum height: 6780 mm [22'-3"] Maximum length: 30480 mm [100'-0"]
- UL/ULC listed drive unit with NEMA-1 motor enclosure and controls and control enclosure conform to ANSI/NEMA ICS1, ICS 2 and ICS 6.
- 1.5 hp / 120 V / 1 ph / 60 Hz
- Travel controlled by limit switches.
- Operation by two simultanuously-activated key switches located on each side of the partition.
- Emergency release mechanism for manual operation during power outage.



#### **Optional Features and Accessories**

- STC 49, 52, 53 or 55 with gypsum board faces and steel backing.
- Powder-coated protective trims and/or track.
- Upgraded wallcoverings: fabric, vertically-ribbed carpet, plastic laminate, full-height marker board, wood veneer, custom finishes.
- Owner-supplied wallcovering (approval required).
- ADA-compliant pass door with flush pulls and roller latch.
- Door options:
  - concealed automatic closer
  - window frame
  - door viewer
  - self-luminous "Running Man" exit sign with green faceplate (standard outside USA, optional in USA) \*
    photoluminescent "EXIT" sign with red faceplate (standard in USA, optional elsewhere) \*
  - photoluminescent "EXIT" sign with green faceplate (optional) \*
  - self-luminous "EXIT" sign with red faceplate (optional) \*
  - self-luminous "EXIT" sign with green faceplate (optional) \*
  - deadbolt lock \*

\* An exit sign and a deadbolt lock will not be installed together on the same door.

- Inset white marker boards.
- Inset chalk boards.
- Inset natural cork tack boards.
- Eraser boxes.
- 3-section pocket door fitted with limit switches to prevent operation of the partition until the pocket door is fully opened.

#### **Horizontal Seals**



**Type FF** Floor clearance : 50 mm [2"] Operating tolerances : +0 mm / -38 mm [+0" / -1 1/2"]



Floor clearance : 50 mm [2"] Operating tolerances : +0 mm / -38 mm [+0" / -1 1/2"]



Vertical Section



843E\_DS\_23-13\_0



#### Plan Views



Wall to wall



Wall to pocket with PA-83 acoustical pocket door



## **Horizontal Section**





### Elevation



- 1- Closure panel
- 2- Single pass door
- 3- Self-illuminated exit sign
- 4- Work surface
- 5- Chalk tray
- 6- Eraser box



Drive Unit





(add 102 mm [4"] to stack area/pocket width)