

**SELECTION & SPECIFICATION DATA**

<b>Generic Type</b>	High solids, two-component, static dissipative aliphatic polyurethane sealer
<b>Description</b>	A two-component, ASTM Type V, aliphatic polyurethane coating. Sealer 30SD offers the outstanding color stability, resistance to UV degradation, and electrostatic dissipative capability. Toughness, impact resistance, and stain resistance are inherent qualities of this topcoat.
<b>Features</b>	<ul style="list-style-type: none"> <li>• Contributes toward satisfying credit for low emitting material under LEED 4.1</li> <li>• Meets California Department of Public Health CDPH/EHLB Standard Method Version 1.2 2017 Compliance Certificates Available Upon Request</li> <li>• Permanent ESD Stability</li> <li>• Meets SCAQMD Rule 1113 for VOC content</li> <li>• High Solids</li> <li>• Excellent Color Stability</li> <li>• Good Stain Resistance</li> <li>• VOC Compliant</li> </ul>
<b>Typical Uses</b>	<ul style="list-style-type: none"> <li>• Clean Rooms</li> <li>• Electronics Manufacturing</li> <li>• Data Processor Rooms</li> <li>• Pharmaceuticals</li> <li>• Testing Labs</li> </ul>
<b>Color</b>	Light Grey, Medium Grey, and Dark Grey are standard. Consult a Dudick or Carboline representative for other available colors. ESD additives alter color at the expense of electrical properties
<b>Finish</b>	Gloss Also available in a Satin finish.
<b>Primer</b>	Steri-Prime, Primer 67LV or others as recommended by Dudick. To increase the thickness of this system apply Steri-Flor GP or Polymer Alloy 2000SD at desired mil rate after priming; then apply one or two coats of Sealer 30 SD for the final finish coat. Contact a Dudick representative for other recommendations.
<b>Dry Film Thickness</b>	4 - 6 mils (102 - 152 microns) DFT
<b>Solids Content</b>	By Volume 78%
<b>Theoretical Coverage Rate</b>	1251 ft <sup>2</sup> /gal at 1.0 mils (30.7 m <sup>2</sup> /l at 25 microns) 313 ft <sup>2</sup> /gal at 4.0 mils (7.7 m <sup>2</sup> /l at 100 microns) 209 ft <sup>2</sup> /gal at 6.0 mils (5.1 m <sup>2</sup> /l at 150 microns) Allow for loss in mixing and application.
<b>VOC Values</b>	<b>As Supplied</b> : <20 g/L

# Sealer 30SD

## PRODUCT DATA SHEET



### SELECTION & SPECIFICATION DATA

#### Chemical Resistance

- Water
- Solvents
- Sodium Hydroxide - 50%
- Dilute Organic/Inorganic Acids
- Oils
- Gasoline
- Jet Fuel

Resistant to splash and spillage of the above chemicals. Not for use in immersion.

### SUBSTRATES & SURFACE PREPARATION

#### Concrete

Refer to the specific primer's Product Data Sheet or System Information Sheet as recommended by your Dudick or Carboline Sales Representative and Technical Service for surface preparation requirements.

### PERFORMANCE DATA (TYPICAL VALUES)

Test Method	Results
Abrasion, ASTM D-4060, CS-17 Wheel	25 mg
Gloss @ 60°	85-90
Impact Resistance (Direct), ASTM D2794	>160 inch lbs
Impact Resistance (Indirect), ASTM D2794	>160 inch lbs
Pencil Hardness	2H

### MIXING & THINNING

#### Mixing

Mix Part A separately for approximately 1 minute before adding Part B. Add Component B to Component A and mix thoroughly for 2-3 minutes to achieve a uniform color and consistency.

DO NOT MIX PARTIAL KITS.

#### Thinning

DO NOT THIN

#### Ratio

2.6:1 (A to B)

#### Pot Life

90 minutes @ 50°F (10°C)

60 minutes @ 75°F (24°C)

45 minutes @ 90°F (32°C)

### APPLICATION EQUIPMENT GUIDELINES

Listed below are general equipment guidelines for the application of this product. Job site conditions may require modifications to these guidelines to achieve the desired results.

#### Brush & Roller (General)

Use a short-nap mohair roller cover with solvent resistant core. For best results, condition roller before application to minimize lint or loose fibers. A high quality solvent resistant brush may be used for hard to reach areas.

### APPLICATION CONDITIONS

Condition	Material	Surface	Ambient	Humidity
Minimum	70°F (21°C)	50°F (10°C)	50°F (10°C)	0%
Maximum	90°F (32°C)	110°F (43°C)	110°F (43°C)	70%

Substrate temperature must be 5°F (3°C) above the Dew Point.

Application in direct sunlight may lead to blistering, pinholes, or wrinkling due to outgassing of air in the concrete and high substrate temperatures. Double priming, shading or evening application may be required.

**Caution:** This product is moisture sensitive in the liquid stage and until fully cured. Protect from high humidity, dew and moisture contact until fully cured. Application and/or curing in humidities above maximum, or exposure to moisture from rain or dew may result in a loss of gloss and/or microbubbling of the product.

### CURING SCHEDULE

Surface Temp.	Tack Free	Foot Traffic	Light Traffic	Heavy Traffic/ Chemical Spillage	Maximum Recoat Time
75°F (24°C)	4.5 Hours	12 Hours	24 Hours	48 Hours	72 Hours

In order to prevent curing problems, thorough and uniform air movement and/or ventilation must be maintained until the system has fully cured. Refer to cure time listed in product data sheet.

### TESTING / CERTIFICATION / LISTING

<b>General</b>	<p><b>TYPICAL ELECTRICAL PROPERTIES</b></p> <p>ANSI/ESD S20.20</p> <p>ESD S 7.1 Surface Resistivity (ohms) @ 50% RH and 73°F</p> <p>10 Volts 106 &gt; &lt; 109</p> <p>100 Volts 106 &gt; &lt; 109</p> <p>ESD STM 97.2 (body voltage generation) (Prostat PFM 711-A with charge plate monitor) &lt; 15 volts @ 50#5% RH</p> <p>To insure surface resistivity properties, the components of Sealer 30 SD must be applied within 30 days of product manufacture. Please refer to storage instructions.</p> <p>Dudick flooring systems can be built to meet or exceed the requirements of Static or Dynamic Coefficient of Friction testing per installation to meet static coefficient of friction requirements for ANSI B101.1 of &gt;0.6 and dynamic coefficient of friction (DCOF)* – Wet ANSI A326.3 of &gt;0.42.</p>
----------------	--

### CLEANUP & SAFETY

**Cleanup** | Use S-10 Cleaning Solvent to clean tools and equipment.

**Safety** | Read and follow all caution statements on this product data sheet and on the SDS. Employ normal safety precautions. Keep container closed when not in use.

### PACKAGING, HANDLING & STORAGE

<b>Packaging</b>	<p><b>1 Gallon Kit:</b></p> <p>Part A: .72 gallons in a 3.5 gal metal pail</p> <p>Part B: .28 gallons in a 1 gal metal can</p> <p><b>2 Gallon Kit:</b></p> <p>Part A: 1.44 gallons in a 3.5 gal metal pail</p> <p>Part B: .56 gallons in a 1 gal metal can</p>
------------------	--

# Sealer 30SD

## PRODUCT DATA SHEET



---

### PACKAGING, HANDLING & STORAGE

---

<b>Shelf Life</b>	Component A & B: 30 Days @ 50°F-75°F (10°C-24°C)
<b>Storage</b>	All products should be stored in a cool, dry area away from open flames, sparks and other hazards. <b>Warning:</b> All Dudick products classified by DOT with either white, yellow or red labels, must not be mixed or stored together as an explosive reaction may occur.
<b>Shipping Weight (Approximate)</b>	1 Gallon Kit - Approx. 15 lbs. (6.8 kg) 2 Gallon Kit - Approx. 27.75 lbs. (12.6 kg)

### WARRANTY

To the best of our knowledge the technical data contained herein is true and accurate on the date of publication and is subject to change without prior notice. User must contact Carboline Company to verify correctness before specifying or ordering. No guarantee of accuracy is given or implied. We guarantee our products to conform to Carboline quality control. We assume no responsibility for coverage, performance, injuries or damages resulting from use. Carbolines sole obligation, if any, is to replace or refund the purchase price of the Carboline product(s) proven to be defective, at Carbolines option. Carboline shall not be liable for any loss or damage. NO OTHER WARRANTY OR GUARANTEE OF ANY KIND IS MADE BY CARBOLINE, EXPRESS OR IMPLIED, STATUTORY, BY OPERATION OF LAW, OR OTHERWISE, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. All of the trademarks referenced above are the property of Carboline International Corporation unless otherwise indicated.