





¹³/₆₄" (90mm) <u>31/2" (89mm)</u> (33/2" (89mm) (83/m) (83/m) (83/m) (83/m) (83/m) (1211m)

USE: Carriage for cantilever gates in stainless steel.

TYPE: Carriage with 5 wheels, monobloc body, stainless steel. FIXING: Use 6 anchor bolts CG-348M16 or suitable plugs (both not supplied). For the dimensions of the concrete base, see the enclosed table. The base enables height adjustment by means of the 4 M16 screws and the special counterplate CGI-05P.

MATERIAL: stainless steel.

RECYCLING: Disposal as ferrous material in accordance with the current laws in the country of installation.

PARTS SUBJECT TO WEAR: Bearings and wheels.

IMPORTANT: The manufacturer reserves the right to modify the characteristics of the product as required without notice. The manufacturer declines any liability for even partial modifications to the product, and the declared performance values are valid only if the installation procedures are carried out by qualified personnel.

| | | TEC | HNICAL CHAR | ACTERISTICS | | | | | | | |
|-------------------------------------------------------|------------------------------|-----------------|-----------------|----------------------------|-------------|--|--|--|--|--|--|
| | | | CGI-350.5P | | | | | | | | |
| WEIG | HT OF PART | | 10,95 Kg | | | | | | | | |
| | RING CAPACI eight on axis | | 2000 Kgf | | | | | | | | |
| MAINTENANCE FREQUENCY | | | | | | | | | | | |
| PRIVATE HOME | BUSINESS | WARE | HOUSE | CONDOMINIUM | CONDOMINIUM | | | | | | |
| | | | | <20 UNITS | > 20 UNITS | | | | | | |
| 2 YEAR* | 2 YEAR * | 1 YE | AR* | 6 MONTHS* | 6 MONTHS * | | | | | | |
| Check the functionality and integrity of carriages. | | | | | | | | | | | |
| Clean lower area of contact between wheels and rail | | | | | | | | | | | |
| | Mak | e sure the carr | riages are inte | gral with the concrete bas | e | | | | | | |
| *The scheme refers to a normal workplace | | | | | | | | | | | |
| (not marine or particularly aggressive environments). | | | | | | | | | | | |

| CGI-350.5P - 5 wheel carriage, monobloc body | | | | | | | | | | | | | | | | | |
|----------------------------------------------|------------------|----------------------|------------------|-----------------------------------------|------------------|------------------------------------------|-----------------|-------------------------------------------|------------------|---------------------------------------------------------------------|--------------------|------------------------------------------------|------------------|------------------------------------------------|------------------|--------------------------------|-----------------|
| HEIGHT | | BASE PLATE LENGTH | | BASE PLATE WIDTH | | AIR GAP (Grade to Bottom of Track) | | FULL HEIGHT (Grade to Top of Track) | | BOLT HOLE SIZE | | BOLT HOLE SPACING (L) (Center-to-Center) | | BOLT HOLE SPACING (W) (Center-to-Center) | | CARRIAGE PLATE THICKNESS | |
| Inch 6½ | mm 166 | Inch 12 | mm 300 | Inch 5 ¹⁵ / ₁₆ | mm 150 | Inch 3¼ | mm 82 | Inch 6¾ | mm 171 | Inch ¹⁵ / ₁₆ x ⁵ / ₈ | mm 24x17 | Inch 9 ⁷ / ₈ | mm 251 | Inch 3 ¹⁵ / ₁₆ | mm 100 | Inch 3/8 | mm 10 |

Illustrations not to scale and are for reference only. Imperial units shown are for reference only, use millimeters for most accurate sizes.

All pictures, technical drawings and related specifications belong to Fratelli Comunello Spa and they are defended by rules of copyright. All uses not expressly authorized will be legally prosecuted. Product specifications are subject to change without notice.



2E Chimney Rock Road • Bridgewater, NJ 08807 | Ph: (908) 757-2323 Fax: (908) 757-3439 | www.duragates.com | info@duragates.com Manufactured by **COMUNELLO**

CGI-350.5P

Large Carriage, Monobloc Body

