RUBEROID® 20 Smooth Membrane

Updated: 8/16





RUBEROID® 20 SMOOTH MEMBRANE

Formerly RUBEROID 20

Description

RUBEROID® 20 Smooth Membrane is a tough, resilient modified bitumen membrane manufactured to stringent GAF specifications. Its core is a strong, resilient non-woven glass mat that is coated with flexible, SBS polymer modified asphalt.

Uses

RUBEROID® 20 Smooth
Membrane is designed for new
roofing and re-cover applications
as well as in the construction of
flashings. RUBEROID® 20 Smooth
Membrane is an ideal base or
interply roofing membrane in
modified bitumen systems,
including GAF CompositeRoof™
and 20/30 systems.

Advantages

- System guarantees are available for up to 20 years.*
- Light weight—Installed roof designs weigh less than 3 pounds per square foot (14.6 kg/m²).
- Durable—Combines the strength of fiberglass reinforcement with the elongation characteristics of SBS modified asphalt.

Advantages (Continued)

- RUBEROID® 20 Smooth Membrane is manufactured by GAF, a company with over 125 years in the roofing business.
- Available as a smooth surface.
 - * See applicable guarantee for complete coverage and restrictions.

Applicable Standards
Meets ASTM D6163, Type I, Grade S
FM Approved
ICC ESR-1274
Miami-Dade County Product Control Approved
State of Florida Approved
Texas Department of Insurance
UL/ULC Classified

pecifications (nominal)
1.5 square (161.4 gross sq. ft.) (15.0 m²)
49.2' (15.34 m)
39.375" (1.0 m)
89.0 lb (40.37 kg)
0.085" (2.1 mm)

This product meets or exceeds the following ASTM D6163, Type I, Grade S, minimum requirements:

Property	Test Method	Value
Tensile Strength @ 0°F (min), lbf/in	ASTM D5147	70
Elongation @ 0°F (min), %	ASTM D5147	1
Low Temperature Flexibility (max), °F	ASTM D5147	0
Tear Strength (min), lbf	ASTM D5147	35
Dimensional Stability, (max) %	ASTM D5147	0.5

