

Tech Data: Wood Veneer

Options
Veneer Species <ul style="list-style-type: none">• Walnut• Rift Cut White Oak• Flat Cut White Oak• Flat Cut Cherry• Flat Cut Mahogany• Specified Flitches• More . . .
Finishes <ul style="list-style-type: none">• Clear• Stain to Match sample• Unfinished• Not available as paint to match

Wood Veneer

Wood veneer that is typically 0.037 inch (0.94 mm) thick is bonded under pressure with an environmentally friendly, PVA-type adhesive to 45 pound, industrial-grade particle board. All edges are edgebanded with veneer edgebanding.

Doors and Pilasters

Wood Veneer Doors and Pilasters are 1-1/4" thick (typical). Shoes are 22 gauge, ASTM A167 stainless steel with satin finish, not less than 3" in height.

Panels

Wood Veneer panels are 7/8" thick (typical).

Door Hardware

Hinges are surface mount and through bolted, strikes/keepers are a slide Indicator latch (typical). Coat hooks, and bumpers are surface mounted. Door pulls are through bolted. All fasteners are tamper proof.

Brackets

Stirrup-type one ear, two-ear, and u-brackets are provided with theft resistant fasteners (typical).

Considerations

- Not guaranteed in wet areas.
- Material availability may affect lead times.
- Veneer color and appearance will vary from log to log.
- Many cleaning solutions are not appropriate for real wood.
- Job site handling should be minimized.

Ironwood Manufacturing reserves the right to make changes in design, material, and documentation without formal notice and without incurring obligation. Consult local and national codes. Conformity and compliance to local and national codes is the responsibility of the installer. Verify all rough in dimensions prior to installation.