

## SERIES SI4306

## TRANSLUCENT PANEL SKYLIGHT SYSTEM




SI4306 thermally-enhanced aluminum poly wall skylight system is designed for use in commercial and residential applications. The 60 mm thick (2 3/8") 10 wall polycarbonate panel infill provides exceptional thermal and structural performance, while allowing diffused light to fill the space without unwanted glare.



## **FEATURES**


- · Thermally-broken aluminum skylight
- 60 mm, 10 wall polycarbonate panel infill
- Standard polycarbonate colors selections: clear and opal
- Maximum panel length: 8' 3"
- · Maximum panel width: 4'
- R-value range from 8 to 13
- · Large missile impact tested
- Standard finishes: AAMA 2603
  - Duracron: Hartford Green, Bronze, Black, Natural Clay, White, Sandstone
- · LEED friendly system including recycled content
- Designed and manufactured in the U.S.A.



## **OPTIONS**


- Custom finishes
  - · Class I anodized: Dark Bronze, Clear
  - Powder coat finish: AAMA 2604-2605
  - Fluoropolymer (50% or 70%): AAMA 2604-2605
  - Cladding options
  - · Dual color or dual finish options
- · Lumira infill for improved U-value














Performance					
Panel Size	NCTL Test #	Impact	DP	Air	Water
			(psf)	(@ 1.6psf)	(@ 5.0psf)
99" x 99"	110-12568-2	Large Missile Impact	±60	.01	15.0

\*Additional depth may be available upon request. Please be sure to visit our website for additional product information.