

JM WHITE EPDM PEEL & STICK POURABLE SEALER POCKETS

Features and Components

- Use:** To seal uneven penetrations through the membrane that are difficult to flash.
- Materials:** Uncured White EPDM (ethylene propylene diene monomer) and plastic inner ring support with a pressure sensitive seam tape around the bottom.
- Color:** White



Component

A
Accessory

Single Ply

Type

FP
Penetration

System Compatibility This product may be used as a component in the following systems. Please reference product application for specific installation methods and information.

Multi-Ply	BUR		APP		SBS			
	HA	CA	HW	HA	CA	HW	SA	MF
Do not use in multi-ply systems								

Single Ply	TPO				PVC			EPDM		
	MF	AD	SA	IW	MF	AD	IW	MF	AD	BA
Compatible with the selected single ply systems above										

Key: HA = Hot Applied CA = Cold Applied HW = Heat Weldable SA = Self Adhered MF = Mechanically Fastened IW = Induction Weld BA = Ballasted AD = Adhered

Peak Advantage® Guarantee Information

Systems
Approved for use in certain JM Peak Advantage Guarantee Systems.

Installation/Application



Self-Adhered

- Prime White EPDM membrane with JM Single Ply Membrane Primer - LVOC or TPO Membrane Primer before applying JM White EPDM Peel & Stick Pourable Sealer Pockets.
- Do not install in direct contact with asphalt or coal tar pitch.
- Refer to JM White EPDM applicator guides or detail drawings for instructions.

Packaging and Dimensions

Size	6" (15.2 cm) diameter
Pockets per Box	6
Weight per Box	8.45 lb (3.83 kg)

Storage

Shelf Life	18 months from manufacture date
Storage Conditions	Store indoors, out of direct sunlight, keep clean and dry prior to use.
Temperature Range	60°F – 80°F (16°C – 27°C)

Technical specifications as shown in this literature are intended to be used as general guidelines only. Please refer to the Safety Data Sheet and product label prior to using this product. The Safety Data Sheet is available by calling (800) 922-5922 or on the web at www.jm.com/roofing. The physical and chemical properties of the product listed herein represent typical, average values obtained in accordance with accepted test methods and are subject to normal manufacturing variations. They are supplied as a technical service and are subject to change without notice. Check with the regional sales representative nearest you for current information.

All Johns Manville products are sold subject to Johns Manville's standard Terms and Conditions, which includes a Limited Warranty and Limitation of Remedy. For a copy of the Johns Manville standard Terms and Conditions or for information on other Johns Manville roofing products and systems, visit www.jm.com/terms-conditions.