

Product Data

Driwall™

Prefabricated Composite Drain 10/013

Part Number: 01-X-0011

Description

Driwall™ Prefabricated Composite Drain 10/013 is a 0.125-inch, “zig-zag” geometric patterned core, drainage mat designed to eliminate hydrostatic pressure from behind foundation walls, retaining walls, planters, plaza decks, and balconies.

The product is produced from an extruded polymer matrix of tangled monofilaments, which are heat-welded at the junctions to form a resilient structure. This product utilizes a non-woven geotextile filter fabric to hold the soil or concrete away from the wall or deck and the core.

When using Driwall™ Prefabricated Composite Drain, aggregate for drainage can be eliminated from a construction site.

Applications

- Plazas, foundation walls, and planters
- Balconies
- Bored rock tunnels with moisture flow
- Will protect soft membranes

Features and Benefits

- Minimal deflection, and no creep or long-term degradation
- Provides a thin profile for tight construction assemblies
- Lightweight and easy to handle

Drainage System

Description	Means of Measurement		Value	
	English	Metric	English	Metric
Core Polymer	Polymeric			
Thickness	Inches	Mm	0.125	3.175

Fabric Properties			
Description	Measurement		Test Method
	English	Metric	
Fabric Color	Charcoal	Polyester	
Weight	1.47 oz/yd ² NW	50 g/m ² NW	ASTM D5261
Thickness	11.8 mils	0.300 mm	ASTM D1777
Grab Tensile Strength	34 lbs	151 N	ASTM D4623
Trapezoid Tear Strength	5 lbs	22 N	ASTM D4533
CBR Puncture Strength	250 lbs	1448 N	ASTM D6241

Flow Rates by Application: ASTM D4716

Hydraulic Gradients:	1.0 Gradient (100% Slope or "Vertical Wall")	0.5 Gradient (50% Slope or "Very Steep Roof / Balcony")	0.02 Gradient (2% Slope or "Industry-Standard Balcony Slope")
Compression Strength	Flow Rate (gpm/ft. of width)	Flow Rate (gpm/ft. of width)	Flow Rate (gpm/ft. of width)
250 psf	5.25	3.53	0.29
500 psf	5.15	3.43	0.28
1,000 psf	4.73	3.12	0.28
2,000 psf	4.49	2.74	0.27
3,000 psf	4.29	2.74	0.27
4,000 psf	3.13	1.98	0.14
5,000 psf	1.12	0.67	0.04

Packaging

Description	Means of Measurement		Value	
	English	Metric	English	Metric
Core Width	Inches	CM	48.0	122
Length	Feet	Meters	100	30.5
Area	Square Feet	Square Meters	400	37.2
Roll Weight	Pounds	Kg	30	13.6

See installation instructions for methods and procedures.

LIMITED WARRANTY: Keene Building Products, Inc. warrants to the initial purchaser only that the goods sold hereunder will be free from defects in material and workmanship and, except as otherwise set forth herein, will conform to the specifications provided. If any failure to meet this warranty appears within one year from the date of shipment of the goods, on the condition that Keene Building Products, Inc. will correct any such failure by either replacing or repairing any defective goods, at Keene Building Products, Inc.'s option.

The preceding paragraph sets forth the exclusive remedy for all claims based on failure of or defect in the goods sold hereunder, whether such failure or defect arises before or during the warranty period and whether a claim, however instituted, is based on contract, indemnity, warranty, tort (including negligence), strict liability or otherwise. The forgoing warranty is exclusive and is in lieu of all other warranties whether written, oral, implied or statutory.



2926 Chester Avenue, Cleveland, OH 44114

877 | 514 | 5336

P 440 | 605 | 1020

KeeneBuilding.com

Info@KeeneBuilding.com

KBP_585001_0725