Model Type RV





RV panel radiators are manufactured in the USA from cold rolled steel, and mounted vertically. The panels are finished in a gloss powdercoat and available in many standard colors and over 100 optional colors. RV panels are made in heights from 20" to 29'-6" and widths from 3" to 70". Standard piping connections are 1/2" NPT for inlet and outlet piping, and 1/8" NPT for vents (3/4" NPT inlets and outlets are available by special order). For more complete RV panel specifications, please refer to the Runtal technical pages.



RV-3

BTUH/FT RATINGS

Energy efficient as well as space saving, RV panels are Runtal's radiant vertical panel. RV panels are useful in foyers and large public entryways, and they provide more comfort at lower room temperatures than convective heaters.

BTUH/ft Ratings @ 65°F EAT					
MODEL	WIDTH	DEPTH	215°F	180°F	140°F
	inches	inches			
RV-2	5.7	1.6	400	290	160
RV-3	8.6	1.6	600	430	250
RV-4	11.5	1.6	800	570	330
RV-5	14.4	1.6	1000	710	410
RV-6	17.3	1.6	1200	850	490
RV-7	20.2	1.6	1400	990	570
RV-8	23.1	1.6	1600	1130	650
RV-9	26.1	1.6	1796	1264	724
RV-10	29.0	1.6	1996	1405	808

Various average water temperatures (AWT) are shown here for convenience, but for more specific conditions use the appropriate correction factor with the 215°F rating. See the technical pages for the correction factor best suited to the design conditions.

MOUNTING SYSTEMS

RV panel radiators are wall mounted with a bracket system that allows for an easy and cost effective installation. All necessary brackets are included with each panel and recessed wall mounting systems are also possible. Please see the RV technical pages for more complete mounting details.

RV-4