NEXT

MODULAR SENSOR SYSTEM

From install and setup, to Al-enhanced imaging, to advanced onboard technologies, NEXT will change your entire camera experience. The powerful Al-based analytics and color forensic evidence—along with the modular design with mix-and-match components—support endless customer applications.



Five-Minute, Three-Step Installation

Our patented snap-and-twist design, combined with the sensor's Al-powered auto-tuning, reduce installation and setup time to under 5 minutes.

Most Powerful Al Imaging on the Market

The sensor's Al Vision adds a layer of intelligence to traditional video for sharper, clearer, less pixelated images with better color integrity, 24/7.

A Complete Communication System Onboard

The camera is packed with intelligence, including customizable LED signal lightbars, as well as 2-way audio, so you can listen in and broadcast instructions.

Practical Analytics for Real-World Problems

Get real-time intel so you can actively detect incidents before they become critical situations, e.g., a loitering analytic could trigger the camera's lightbars and warning messages.

Unlimited Mix-and-Match Applications

Just a handful of unique components can be mixed and matched as your needs evolve; all components are completely modular, hot-swappable, and universally interchangeable.



The Easiest Camera You'll Ever Install

Screw. Snap. Twist. Done.

Install each camera in five minutes or less! Here's how...



PoE Status Indicator

a potential power issue.

In addition to providing power/data

status, an LED on the network

hub indicates the power level

status, so you can self-diagnose

Four-Screw Install

Affix the base to its surface with just four screws, then simply snap and twist the remaining components together—no additional tools or hardware required.



Automated Image Tuning

The camera's Al Vision does all the fine tuning automatically, optimizing the camera for its environment without manual intervention.



Remote Positioning

Direction Indicators

the camera incorrectly.

Physical indicators on the various

orient them for fast installation,

and make it impossible to install

components allow you to intuitively

Set up the perfect field-of-view from anywhere within seconds. This is a one-person job, with no ladders or cell phones required!



Single-Step Corridor Mode

The imager automatically orients itself to corridor/hallway mode.



IP Address on the Hub

The camera's IP address resides on the network hub (which manages up to 4 sensors); there's no need to allocate a new address if you add or replace a camera sensor.



Factory-Sealed Camera

This eliminates risk of improper installation, water and dust intrusion, and even fingerprints on the lens.





The Base





The Camera Sensor

Unparalleled Video Clarity in Any Environment

No Light? No Problem!

Any camera can deliver a great picture in ideal conditions. But how a camera responds when lighting conditions are compromised makes all the difference. NEXT incorporates Al Vision for sharper, clearer images—always in color—in even the most demanding circumstances.





Real-Time Auto-Tuning

NEXT's Al Vision does all the fine tuning automatically, constantly optimizing the camera for its environment and lighting, in real-time, without manual intervention.



See Colors in the Dark

The camera's Artificial Intelligent Retina (AI-R) lets you see colors in as low as 0.02 lux, so you can quickly detect incidents and identify suspects, even in near-dark conditions.



Leverage Color-Based Analytics

Perform searches based on things like the color of a person's shirt and/or pants, or the color of a vehicle, even in the dark (when traditional cameras switch to black & white).



Say Goodbye to IR

Eliminate the inconveniences that come with IR—like lens spotting, IR flare and unusable video in the rain.

The Smartest Camera in the Room

An Entire Communication System Packaged into a Single Device

With one of the smallest footprints in the industry, this camera is bundled with intelligent features that render it more than just a camera—it's a self-contained solution with an advanced onboard communication system.

XVICON

)))(((

Powerful Microphones

Two powerful microphones let you hear what's going on within 50 feet (15 m) in any direction of the sensor.



360° Speakers

Two commercial-grade speakers emit customized messages up to 50 feet (15 m) in all directions, so you can communicate pre-recorded instructions and warnings PLUS direct talk-down in real-time.



AI Analytics

Real-time intel lets you proactively detect and prevent incidents before they become critical situations.

Programmable LED Signal Lightbars

Four programmable lightbars can communicate situational awareness status, e.g., flashing red for warning, solid green for all-clear, blue for shift change, amber for person in lobby, etc.

When used with Vicon's Anavio platform, each NEXT sensor comes with a free Anavio license.

Will These Features Work With My VMS?

Yes! NEXT is certified for compatibility with the industry's leading VMS platforms, allowing you to leverage all of these innovative features without having to rip and replace your existing systems and infrastructure.





Your Modular NEXT Ecosystem

Here's How It Comes Together

The system's modular design allows it to adapt to your unique needs, supporting a myriad of applications with interchangeable, hot-swappable, mix-and-match components.

The Mounts*







Pendant

Box

Conduit

In-Ceiling

Wall

Electrical Box Adaptor

The Fixtures









Solo

Duo

Two

Quad

The Camera Sensors



One





Three



Four









- A single network hub (and IP drop) powers from 1-4 sensors and accommodates any fixture.
- All mounts and fixtures are universally compatible with the network hub and camera sensors.
- Each mount and fixture can be mixed and matched—hot swappable—as your requirements change.
- The installation process is identical for every configuration, significantly reducing the learning curve. Once you learn how to install one, you can install any!

* Fixture Kits can be surface-mounted directly to a ceiling, no mount required.



Pendant Mount, Solo Fixture and One Camera Sensor shown









Camera Sensor



System on Chip (SoC)

SoC	Al Vision Processor
Neural Net Processing	20 TOPS
Memory	2GB DDR + 4GB eMMC

Imaging	
Image Sensor	1/1.8"
Resolution	Ultra HD 4K (3840 x 2160)
Image Signal Processing (ISP)	Al De-noise, Neural Net HDR
Image Settings	Automatic; self-tuning with Al signal processing
Minimum Illumination	Low-light color 0.02 lux
IR	Artificial Intelligent Retina (AI-R)
Day/Night	Al ISP in full color
WDR	120 dB True WDR
Shutter Speed	Auto (full frame rate)
On-Screen Display	Date and time Camera name/text string (up to 85 characters, customizable) OSD position setting Configurable font color, background color, and character size

Positioning	
Lens Positioning	Remotely adjustable pan, tilt, roll, zoom (PTRZ)
Pan (Yaw)	+/- 175°, > 10°/s
Tilt (Pitch)	15° ~ 95°, > 10°/s
Roll	-5° ~ 95°, > 10°/s
Presets	2
Orientation	Landscape and portrait (corridor) modes
Privacy Zones	8 zones

Video	
Image Compression	H.265, H.264, MJPEG
Maximum Frame Rate	30 fps
Resolution & Streams 4 streams @ 30fps 3840 x 2160 1280 x 720 720 x 408 384 x 216	4 streams @ 25fps 3840 x 2160 1920 x 1080 1280 x 720 720 x 408
Maximum Streams	10 at 8 Mbps per stream (80 Mbps total)
Customized Video Profile	CBR/CVBR
Data Rate	500~12000 bps

Lens	
Field-of-View	Wide: 109.8° (H) x 61.8° (V) Tele: 57.2° (H) x 32.2° (V)
Focal Range	4.42 mm - 9.51 mm (motorized varifocal with autofocus)
Focus Control	Auto
Aperture	f1.35
Iris	P-Iris (Auto)

Communications	
Audio Compression Format	A-Law/µ-Law, Opus
Microphones	2 microphones; up to 50 ft (15 m)
Speakers	2 speakers; up to 50 ft (15 m)
Pre-Recorded Messages	10 customizable audio files
Direct Talk-Down	Yes
LED Signal	4 RGBW Lightbars; up to 50 ft (15 m)

Camera Sensor cont'd

System Integration	
Real-Time Analytics	Motion detection, tamper/blur detection, tripwire/line detection cross detection, intrusion detection, crowding detection, loitering detection, tailgating detection
Forensic Analytics	Museum search, classification (people, vehicle, animal), vehicle color, people attributes (lower and upper body clothing color)
Onboard Storage	microSDXC (sold separately) Up to 1TB per Sensor



Network Hub

System on Chip (SoC)

SoC	Dedicated Network Processor
Memory	1GB DDR + 4GB eMMC
Sensor Management (1-4 Sensors)	Management of network settings, sensor configuration, backup and restoration of settings, firmware upgrades

Network

Ethernet	10/100/1000 Mbps
Connector	RJ45 (IP67 coupler)
Control	Reset/Default button

Electrical PoE Solo/Duo Sensor: 802.3at Trio/Quad Sensor: 802.3bt LED Status Indicator Power/Data Power level detection status (af, at, bt)

Alarms

Input/Output

1 dry contact/1 dry relay output (terminal block at pigtail)

System Camera Sensor + Network Hub



General

Power Consumption Solo: 18.4 W (802.3at) Duo: 27.7 W (802.3at)

Trio: 37.7 W (802.3bt) Quad: 47 W (802.3bt)

Protocols

IPv4, IPv6, HTTP, HTTPS, UPnP, DNS, DDNS, NTP, RTSP, RTP, TCP, UDP, ICMP, IGMP, DHCP, ARP, IEEE 802.1X, FTP, RTCP, SMTP, SNMP v1/2c/3, QoS, TLS, LDAP, ONVIF Profile G/T/S/M

Utilities

PRONTO network configuration and firmware management (for VMS use)

Web Browser

Safari, Mozilla Firefox, Chrome, Microsoft Edge

Security

Password protection, IP address filtering, HTTPS, IEEE 802.1X network access control, Digest authentication, Secure boot, SB-327 support

Account Management	Multiple user groups (10 admin/operator/user)
Profile Management	User configurations import/export
Firmware Update	Web update, PRONTO, Over-the-Air (OTA) for Anavio
Language	English
Environmental	
Operating Temperature	-40°F to 131°F (-40°C to +55°C)
Cold Start Temperature	-40°F (-40°C)
Storage Temperature	-40°F to +140°C (-40°C to +60°C)
Operating Humidity	90%, non-condensing
Weather Resistance	IP67
Vandal Resistance	IK10

Regulatory

CE EN 55032, EN 55035, EN 61000-3-2, EN 61000-3-3, IEC 61000-4-2, IEC 61000-4-3, IEC 61000-4-4, IEC 61000-4-5, IEC 61000-4-6, IEC 61000-4-8, IEC 61000-4-11, UKCA FCC FCC, Part 15, Subpart B, Class A RoHS Directive 2011/65/EU and EN 63000-2018; EU Directive 2015/863/EU UL 62368-1 and CSA C22.2 UL No. 62368-1:19 **Country of Origin** Taiwan Warranty 5 years

Dimensions + Construction

Solo Fixture Kit + Camera Sensor

Camera Sensor Material: Aluminum Magnesium Alloy and Polycarbonate (factory sealed)

Solo Fixture Material: Engineered Polymer

4.38 in. (111.5 mm)

Combined Weight: 1.63 lbs (0.74 kg)

Color: Black



Compatible With: Conduit Mount, Wall Mount, Pendant Mount, Electrical Box Adaptor, Pole Mount, Corner Mount, In-Ceiling Mount

Trio Fixture Kit + Camera Sensors

Camera Sensor Material: Aluminum Magnesium Alloy and Polycarbonate (factory sealed)

5.25 in.

(133.6 mm)

Trio Fixture Material: Engineered Polymer

Combined Weight: 5.25 lbs (2.9 kg)

Color: Black

Compatible With: Conduit Mount, Wall Mount, Pendant Mount, Electrical Box Adaptor, Pole Mount, Corner Mount



8.97 in. (228 mm) Depth 8.4 in. (213.3 mm)

4.5 in. (114.4 mm)

Conduit Box Mount

Material: Aluminum Magnesium Alloy with rubber conduit plugs

Weight: 0.93 lb (0.42 kg)



Color: Black

Pendant Mount

Material: Aluminum Magnesium Alloy

4.44 in. (113 mm)

Color: Black

Weight:

0.24 lb (0.11 kg)

2.5 in.

(63.6 mm)

Less than 1/2" thick

Compatible with 1.5" female interfaces

Electrical Box Adaptor

Material:

Color: Black

Aluminum Magnesium Alloy plate with Engineered Polymer trim ring

Weiaht: 0.21 lb (0.095 kg)



5.66 in. (144 mm)

Duo Fixture Kit + Camera Sensors

Camera Sensor Material: Aluminum Magnesium Alloy and Polycarbonate (factory sealed)

5.25 in.

(133.6 mm)

Duo Fixture Material: Engineered Polymer

Combined Weight: 3.5 lbs (1.6 kg)

Color: Black



Depth 4.44 in. (113 mm)

Compatible With: Conduit Mount, Wall Mount, Pendant Mount, Electrical Box Adaptor, Pole Mount, Corner Mount

Quad Fixture Kit + Camera Sensors

Camera Sensor Material: Aluminum Magnesium Alloy and Polycarbonate (factory sealed)

5.25 in.

(133.6 mm)

Quad Fixture Material: Engineered Polymer

Combined Weight: 7 lbs (3.2 kg)

Color: Black

Compatible With: Conduit Mount, Wall Mount, Pendant Mount, Electrical Box Adaptor, Pole Mount, Corner Mount



9.04 in. (229.8 mm) Depth 9.04 in. (229.8 mm)

8.29 in. (210.8 mm)

Wall Mount

Material:

Engineered Polymer body and Aluminum Magnesium mount Interface

Weight: 1.04 lbs (0.47 kg)

Color:

Black



Material: Zinc-Plated Cold Rolled Steel bracket and Engineered Polymer trim ring

Weight: 0.97 lb (0.44 kg) 3.05 in. (77.5 mm)

Ø 4.44 in.

(113 mm)



Color: Black

Ordering Information

Camera Sensor

VNX-SN-VRS1-0

4K (8 MP) 4.42 mm - 9.51 mm P-Iris lens with 2.15x optical zoom.



Solo Fixture Kit

VNX-FX-SOBK-0

Includes solo fixture, network hub, and base. Camera sensor and mount (optional) ordered separately.



Trio Fixture Kit

COMING SOON!

VNX-FX-TRBK-0

Includes trio fixture, network hub, and base. Camera sensors (3) and mount ordered separately.



Wall Mount

VNX-AC-WBBK-0 Use this when mounting any of the fixtures on a wall. Also compatible with Conduit Box Mount.



In-Ceiling Mount

VNX-AC-ICBK-0 Use this when recessing a single sensor into a ceiling.



Conduit Box Mount

VNX-AC-CBBK-0

Use this when you need to protect the cables from the elements, vandalism, etc. Also compatible with Wall Mount.



COMING SOON!

Pole Mount

VNX-AC-PMBK-0

Use this when mounting any of the fixtures to a pole (also requires the VNX-AC-WBBK-0 Wall Mount).



NEXT Edge Storage

VNX-EL-SD1T-0

One 1TB card required per camera sensor for Anavio/edge recording.

Duo Fixture Kit

VNX-FX-DUBK-0

Includes duo fixture, network hub, and base. Camera sensors (2) and mount ordered separately.

Includes guad fixture, network hub,

and base. Camera sensors (4) and

mount ordered separately.



Pendant Mount

VNX-FX-QDBK-0

VNX-AC-PCBK-0

Use this when suspending any of the fixtures from the ceiling. Contains industry-standard 1.5" NPT pipe thread for extending drop length.



VNX-AC-APBK-0 Use this adaptor plate when mounting any of the fixtures to 4S, double-gang and octagon boxes.



Corner Mount

COMING SOON!

VNX-AC-CMBK-0

Use this when mounting any of the fixtures to a corner (also requires the VNX-AC-WBBK-0 Wall Mount).



Specifications subject to change without notice. Vicon and its logos are registered trademarks of Vicon Industries Inc. Copyright © 2025 Vicon Industries Inc. All rights reserved.

8009-7344-02 Rev 00



vicon-security.com



COMING SOON!