
KEY TO PRECISION AUTOMATIC ELECTRIC DISAPPEARING STAIRWAY



MEASUREMENTS

0	>
ı	38*

č	
1	

D	١
ı	

×	"
1	ı

* MEASURED FROM FLOOR TO FLOOR

NOT TO SCALE

1		1		ì	\
(<	J	֚֚֚֚֚֚֚֚֚֚֚֚֚֚֚֚֚֚֡֝֝֝֝֟֝֝֟֝֝֟֝֝֟֝֝֟֝֟֝֟֝	,)
www.PrecisionLadders.com	Ph: (423) 586-2265 Fax: (423) 586-2091	P.O. Box 2279 Morristown, TN 37816-2279	ecision Ladders, LLC		
	91 CHECKED BY:		BUILT BY:		DWG. CHECK
SEX	DRAWN BY:		PURCHASE ORDER		ARCH'T OR ENG'R.
12/23/09	DATE / C Z		WORK ORDER		PROJECT
AE- 1	MODEL# QTY.		PURCHASER		
			SERIAL#		PRECISION REP

AEKEY

ALUMINUM CONSTRUCTION

STANDARD:

ROUGH OPENING IN CEILING 30" X 72"

 Θ

FRAME 1/8" STEEL X 28-1/2" X 71" X (USE 52' ANGLE FRAME IF DROPPED CEILING IS 13" OR MORE FOR HEAD CLEARANCE) EXACT FINISHED CEILING HEIGHT ± 1/2": EXACT FLOOR TO FLOOR DIMENSION ± 1/2":

- HAND-GUIDE RAILS 1-1/16"OD GALVANIZED
- (d) (w) (4) SEALED BALL BEARINGS
- 1/3 HP 115-VOLT INSTANTLY REVERSIBLE MOTOR DIRECT-CONNECTED TO A REDUCTION GEAR DRIVE, COMPLETE WITH CONTACTORS & PREWIRED TO CONTROL SWITCHES.
- **(5)** STRINGERS 7" X .230" CHANNEL
- TREADS 6" X 20-3/16" X .225" CHANNEL COVERED WITH NON-SKID SAFETY TREAD
- DOOR PANEL 1/8" SHEET ALUMINUM
- BATTERY BACK-UP (NOT SHOWN)
 (USED IN CASE OF POWER FAILURE TO LOWER ONLY) EACH STAIRWAY IS FACTORY TESTED BEFORE SHIPMENT & IS SHIPPED IN A HEAVY PROTECTIVE CRATE.

<u>OPTIONS-(Check_if_Required)</u>

WARNING BUZZER, WHEN STAIR IS IN USE KEY SWITCH AT LOWER LEVEL